



CARRYING CASES

Infinity 20 (FX 8-1/2)

Catalog #: 50500



Description

The Infinity case is an attractive option for product protection and is easily customized with engraving, printing, labeling, die-cut foam, custom colors and in-mold labeling and decorating. Constructed of high-density polyethylene (HDPE), the Infinity case resists most chemicals and gasoline. The case offers a natural dust seal and double-wall protection in the lid and base that automatically creates an interior impact barrier for crush resistance. A dual latch system provides easy latching for security, even in harsh conditions. Interior Dimensions: 17 3/4" x 12 5/8" x 7 1/2" (45.09 x 32.07 x 19.05 cm), Exterior Dimensions: 20" x 15" x 8 1/2" (50.80 x 38.10 x 21.59 cm). Interior Depth: Lid: 3 1/4" (8.26 cm), Base: 4 1/4" (10.80 cm). Logo area is (L x W) 5 x 2 inches.

Specifications

Catalog # 50500

Stock Number 50500

My Case Builder IDFX8

Division Code 618

Style FX 8 1/2

Compartments 1

Color Black

Material Polyethylene (HDPE)

(S) Inside Overall: 17 3/4" x 12 5/8" x 7 1/2"

(M) Inside Overall: 45.09 x 32.07 x 19.05 cm

(S) Outside Overall: 20" x 15" x 8 1/2"

(M) Outside Overall: 50.80 x 38.10 x 21.59 cm

(S) Outside Length: 20.00000

(S) Outside Width: 15.00000

(S) Outside Depth: 8.00000

(M) Outside Length: 50.80000

(M) Outside Width: 38.10000

(M) Outside Depth: 21.59000

(S) Inside Length: 12.62500

(S) Inside Width: 17.75000

(S) Inside Depth: 7.50000

(M) Inside Length: 0.00000

(M) Inside Width: 0.00000

(M) Inside Depth: 0.00000

Accessories: 1070|1066|1077