

Accessories CI-K2-PKZ0

Part no. CI-K2-PKZ0

Article no. 219653

For PKZM0 motor-protective circuit-breakers

Program

			Cover with aperture dimensioned to accommodate front of breaker IP40, when mounted turned through 90° to left/right
Protection type			IP41 when mounted vertically
For use with			PKZM0-... +NHI or AGM +U or A (undervoltage or shunt release) +NHI-E +L-PKZ0 (2 off)
Notes M25 metric cable entry knockout, top and bottom Push-through cable entry diaphragm top, bottom, in the back plate and for control cable entry. CI-K2 insulated enclosure includes N and PE terminal.			


Approbationen

UL approval	No
CSA approval	No
Specially designed for NA	No


Technical data according to ETIM 4.0

Width		mm	80
Design			surface mounting
Height		mm	158
Depth		mm	100
With transparent cover			No
Suitable for emergency stop			No
Housing material			Insulated material
Degree of protection (IP)			IP40

Dimensions



Drilling dimensions



Additional product information (links)

IL03402002Z (IL03402002Z) Motor-protective circuit-breaker with insulated enclosures

ftp://ftp.moeller.net/DOCUMENTATION/AWA_INSTRUCTIONS/IL03402002Z2010_10.pdf

Motor starters and "Special Purpose Ratings" for the North American market

http://www.moeller.net/binary/ver_techpapers/ver953en.pdf

Busbar Component Adapters for modern Industrial control panels

http://www.moeller.net/binary/ver_techpapers/ver960en.pdf

