

Distributed by:







www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 300792

Date	Rev.	Description

Size : 120 x 120 x 38
Unit : mm



Terminal or Lead Wire Type

Impedance Protection

Spec. Model	Rated Voltage V	Frequency Hz	Input Power W	Rated Current A	Locked Current A	Speed RPM	Maximum Air Flow m ³ /min.	Maximum Air Flow CFM	Maximum Pressure mmH ₂ O	Maximum Pressure InchH ₂ O	Noise dB	Weight kg
UF12A10-H	100V	50	19	0.24	0.33	2700	2.6	92	8.0	0.32	42	0.53
		60	16	0.20	0.27	3100	3.0	106	8.0	0.32	46	
UF12A11-H	115V	50	14	0.20	0.27	2700	2.6	92	8.0	0.32	42	0.53
		60	12	0.16	0.23	3100	3.0	106	8.0	0.32	46	
UF12A20-H	200V	50	19	0.12	0.17	2700	2.6	92	8.0	0.32	42	0.53
		60	16	0.10	0.13	3100	3.0	106	8.0	0.32	46	
UF12A23-H	230V	50	17	0.10	0.14	2700	2.6	92	8.0	0.32	42	0.53
		60	15	0.08	0.12	3100	3.0	106	8.0	0.32	46	
UF12A11-M	115V	50	14	0.18	0.20	2500	2.4	85	6.5	0.26	40	0.53
		60	12	0.17	0.19	2750	2.6	92	7.0	0.28	42	
UF12A23-M	230V	50	17	0.09	0.10	2500	2.4	85	6.5	0.26	40	0.53
		60	15	0.08	0.09	2750	2.6	92	7.0	0.28	42	
UF12A11-L	115V	50	14	0.16	0.18	2100	2.1	75	4.0	0.16	36	0.53
		60	12	0.15	0.16	2300	2.3	82	4.1	0.16	38	
UF12A23-L	230V	50	17	0.08	0.09	2100	2.1	75	4.0	0.16	36	0.53
		60	15	0.07	0.08	2300	2.3	82	4.1	0.16	38	

DCC. NO.
A4 DRAWING NO.

MATERIAL			GOLDSUN ELECTRONICS CO., LTD.			
			JAMECO NO.	GOLDSUN NO.		
			300792	UF12A11-L		
DRWN	Kiki Chen	DATE	Description			Rev.
CHK	Ada Zheng	DATE	AC FAN			1
APVD	Chesley Chang	DATE	UNIT:	SCALE:	SHEET 1 OF 1	CAS No:
			mm			ERN No: