

PRODUCT DATASHEET



TUF4AAPE

BRIGHT

- 4 white LEDs provide 35 lumens of light
- Tight white spot



TOUGH

- Survives a 2-meter drop
- Rugged shatterproof lens



RELIABLE

- Keeps cost of ownership low with impressive 23-hour run time
- LEDs never need replacing



WEATHERPROOF

- Meets IEC 60529 IPX4 standards for water resistance
- Ideal for outdoor applications



The Toughest Flashlight You'll Ever Need™ - ideally suited for mid-sized jobs in smaller areas, the Energizer® Hard Case Professional® LED Project Light is easy to hold and pack up. Its bright white spot puts light where you need it most and the shatterproof lens shelters the LEDs. Made from impact resistant ABS plastic with steel sides and a shock absorbing rubber overmold, the light survives a 2-meter drop. It is water resistant, making it ideal for many outdoor applications. Finally, an impressive 23-hour run time keeps cost of ownership low.




Before Using Your Flashlight:
Please read all instructions and cautionary markings on the package and light

Product Detail:

Designation:	Energizer Hard Case Professional LED Project Light
Model:	TUF4AAPE
Color:	Black and Dark Grey
Power Source:	Four "AA"
ANSI / NEDA:	15 Series
Lamp:	Four Nichia® LEDs
Lamp Life (hr):	Lifetime
Lamp Output (lumens):	35
Beam Distance (m):	55
Peak Beam Intensity (cd):	850
Run Time (h:mm):	23
Durability:	Survives a 2-meter drop
Typical Weight:	333 grams without batteries
Dimensions (mm):	225 x 76

Performance:



Tested according to ANSI / NEMA FL 1 Standards.

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication
Contents herein do not constitute a warranty
©Energizer / All Rights Reserved