

For use in all areas of industrial manufacturing and in quality control

8305-20



		N-m	lbf-ft	[- mm -]	المقياس	mm	Signal	
		0,8-4	7-35 lbf-in	244	0,1 N-m / 1 lbf-in	61	optional	500
		2,4-12	21-105 lbf-in	244	0,5 N-m / 2 lbf-in	61	optional	500
		5-25	44-220 lbf-in	244	1 N-m / 10 lbf-in	69	optional	500
		8-40	72-360 lbf-in	244	1 N-m / 10 lbf-in	69	optional	500
		16-80	12-60	435	2 N-m / 1 lbf-ft	86	optional	1350
		40-200	30-160	515	5 N-m / 5 lbf-ft	86	optional	1400
		80-400	60-300	710	10 N-m / 10 lbf-ft	111	standard	3150
		160-800	120-600	1000	20 N-m / 20 lbf-ft	123	standard	4850
196790	8305-14	280-1400	200-1000	2040	25 N-m / 25 lbf-ft	138	standard	16690
196804	8305-20	400-2000	300-1500	2040	50 N-m / 50 lbf-ft	138	standard	16690