




Selco 1/2" Disc Thermostats Automatic Reset



Cross Reference Chart

| Thermdisc | Elmwood                        | Klixon |
|-----------|--------------------------------|--------|
| 36T       | 2450<br>3450<br>2455R<br>3455R | 1NT01  |

Snap action bimetal thermostats open or close a circuit at a factory pre-set temperature. **Typical Applications Include:** Power supplies, amplifiers, engines, appliances, fans, freezers and vending machines. All have solder terminals except for QC which are 0.250 quick connect. 125 VAC, 15 amps resistive; 250 VAC, 10 amps resistive. 100,000 life cycles.

Open On Rise (Normally Closed)




| Stock No. | Mfr.'s Type | Open    | Close   | EACH  |       |       |
|-----------|-------------|---------|---------|-------|-------|-------|
|           |             |         |         | 1-24  | 25-49 | 50-99 |
| 557-0001  | OA-60       | 60°F±5  | 40°F±8  | 10.84 | 8.33  | 5.50  |
| 557-0002  | OA-85       | 85°F±5  | 70°F±8  | 10.84 | 8.33  | 5.50  |
| 557-0003  | OA-110      | 110°F±7 | 80°F±6  | 10.84 | 8.33  | 5.50  |
| 557-0004  | OA-120      | 120°F±5 | 90°F±8  | 10.84 | 8.33  | 5.50  |
| 557-0005  | OA-130      | 130°F±5 | 100°F±8 | 10.84 | 8.33  | 5.50  |
| 557-0006  | OA-140      | 140°F±5 | 110°F±8 | 10.84 | 8.33  | 5.50  |
| 557-0007  | OA-150      | 150°F±5 | 120°F±8 | 10.84 | 8.33  | 5.50  |
| 557-0008  | OA-160      | 160°F±5 | 130°F±8 | 10.84 | 8.33  | 5.50  |
| 557-0009  | OA-170      | 170°F±5 | 140°F±8 | 10.84 | 8.33  | 5.50  |
| 557-0010  | OA-175-QC   | 175°F±5 | 145°F±8 | 10.84 | 8.33  | 5.50  |
| 557-0011  | OA-180      | 180°F±5 | 150°F±8 | 10.84 | 8.33  | 5.50  |
| 557-0012  | OA-190      | 190°F±5 | 160°F±8 | 10.84 | 8.33  | 5.50  |
| 557-0013  | OA-190-QC   | 190°F±5 | 172°F±8 | 10.84 | 8.33  | 5.50  |
| 557-0014  | OA-200      | 200°F±5 | 170°F±8 | 10.84 | 8.33  | 5.50  |
| 557-0015  | OA-210      | 210°F±6 | 180°F±8 | 10.84 | 8.33  | 5.50  |
| 557-0016  | OA-220      | 220°F±6 | 190°F±8 | 10.84 | 8.33  | 5.50  |
| 557-0017  | OA-250      | 250°F±7 | 220°F±8 | 10.84 | 8.33  | 5.50  |
| 557-0018  | OA-280-QC   | 280°F±7 | 250°F±8 | 10.84 | 8.33  | 5.50  |
| 557-0019  | OA-300      | 300°F±7 | 270°F±8 | 10.84 | 8.33  | 5.50  |
| 557-0020  | OR-350-QC*  | 350°F±8 | 320°F±8 | 10.84 | 8.33  | 5.50  |
| 557-0021  | OR-365-QC*  | 365°F±8 | 335°F±8 | 10.84 | 8.33  | 5.50  |

\*OR Series have 0.57" height.

Close On Rise (Normally Open)

| Stock No. | Mfr.'s Type | Close   | Open    | EACH  |       |       |
|-----------|-------------|---------|---------|-------|-------|-------|
|           |             |         |         | 1-24  | 25-49 | 50-99 |
| 557-0022  | CA-60       | 60°F±7  | 40°F±8  | 10.84 | 8.33  | 5.50  |
| 557-0023  | CA-85       | 85°F±7  | 70°F±6  | 10.84 | 8.33  | 5.50  |
| 557-0024  | CA-100      | 100°F±7 | 70°F±6  | 10.84 | 8.33  | 5.50  |
| 557-0025  | CA-120      | 120°F±7 | 90°F±6  | 10.84 | 8.33  | 5.50  |
| 557-0026  | CA-130-QC   | 130°F±7 | 110°F±6 | 10.84 | 8.33  | 5.50  |
| 557-0027  | CA-140      | 140°F±7 | 110°F±6 | 10.84 | 8.33  | 5.50  |
| 557-0028  | CA-160      | 160°F±7 | 130°F±6 | 10.84 | 8.33  | 5.50  |
| 557-0029  | CA-170      | 170°F±7 | 140°F±6 | 10.84 | 8.33  | 5.50  |
| 557-0030  | CA-175-QC   | 175°F±7 | 145°F±6 | 10.84 | 8.33  | 5.50  |
| 557-0031  | CA-180      | 180°F±7 | 150°F±6 | 10.84 | 8.33  | 5.50  |
| 557-0032  | CA-190-QC   | 190°F±7 | 172°F±6 | 10.84 | 8.33  | 5.50  |
| 557-0033  | CA-200      | 200°F±7 | 170°F±6 | 10.84 | 8.33  | 5.50  |
| 557-0034  | CA-225      | 225°F±8 | 195°F±6 | 10.84 | 8.33  | 5.50  |

Selco 1/2" Disc Thermostats Manual Reset



Cross Reference Chart



| Thermdisc | Elmwood          | Klixon |
|-----------|------------------|--------|
| 36T       | 2455RM<br>3455RM | 1NT08  |

This manual reset safety switch is ideal as the back up unit. It can be manually reset 30% below its operating temperature. 125 VAC, 15 amp/250 VAC, 10 amp resistive. 6000 life cycles.

| Stock No. | Mfr.'s Type | Open On Rise | EACH  |       |       |
|-----------|-------------|--------------|-------|-------|-------|
|           |             |              | 1-9   | 10-24 | 25-99 |
| 557-0045  | OA-150M*    | 150°F±10     | 11.65 | 9.34  | 6.50  |
| 557-0046  | OA-180M     | 180°F±10     | 11.65 | 9.34  | 6.50  |
| 557-0047  | OA-194M     | 194°F±10     | 11.65 | 9.34  | 6.50  |
| 557-0048  | OA-250M     | 250°F±10     | 11.65 | 9.34  | 6.50  |
| 557-0049  | OA-225M*    | 225°F±10     | 11.65 | 9.34  | 6.50  |
| 557-0050  | OA-302M*    | 302°F±10     | 11.65 | 9.34  | 6.50  |

\*.250 quick connect terminal.

Selco 1/2" Disc High Temperature Thermostat




- Features
- High Temperature Case
  - ISO9000 Certification
  - Quick and Easy Installation

- Applications
- Vacuum Cleaners
  - Gas Furnaces
  - Heaters


This snap-action bimetal disc was developed in a ceramic case to handle extremely high temperatures. The new increased factory calibrated set points are available up to 500°F (260°C). The contacts can either open or close on temperature rise. All models are 100% temperature tested before leaving the factory. **Specifications. Electrical Rating:** 125 VAC, 15 A, resistive; 250 VAC, 10 A, resistive 100,000 cycles. **Operating Temperature Range:** 104°F-500°F (40°C-260°C). **Differential:** 27°F-90°F (15°C-50°C). **Environmental Temperatures:** -4°F-554°F (-20°C-290°C). **Insulation Resistance:** 100 MΩ or more (with a 500 VDC megger). **Circuit Resistance:** 50 MΩ or less (initial value). **Dielectric Strength:** 1500 VAC/1 minute.

| Stock No. | Mfr.'s Type | Open     | Close    | EACH  |       |       |
|-----------|-------------|----------|----------|-------|-------|-------|
|           |             |          |          | 1-9   | 10-24 | 25-99 |
| 557-0058  | ORA-400-QC  | 400°F±10 | 340°F±12 | 11.65 | 9.34  | 6.50  |
| 557-0059  | ORA-425-QC  | 425°F±10 | 375°F±15 | 11.65 | 9.34  | 6.50  |
| 557-0060  | ORA-450-QC  | 450°F±12 | 370°F±15 | 11.65 | 9.34  | 6.50  |
| 557-0061  | ORA-500-QC  | 500°F±20 | 420°F±20 | 11.65 | 9.34  | 6.50  |




Selco 3/4" Disc Thermostats



SEF, SEL




KISO, SES



Cross Reference Chart

| Thermdisc | Elmwood | Klixon |
|-----------|---------|--------|
| 60T       | 2500    | 20600  |



Direct sensing thermostats are larger giving them a powerful bimetallic disc and higher electrical rating. Ideal for H.V.A.C. systems and industrial applications. 120, 240, 227 VAC at 25 amps, resistive, 100,000 cycles. 120 VAC, 10 F.L.A., 60 L.R.A., inductive, 100,000 cycles. 240 VAC, 5 F.L.A., 30 L.R.A., inductive, 100,000 cycles.

| Stock No. | Mfr.'s Type | Open  | Close | EACH  |       |       |
|-----------|-------------|-------|-------|-------|-------|-------|
|           |             |       |       | 1-24  | 25-49 | 50-99 |
| 557-0200  | SE-F120     | 100°F | 120°F | 12.24 | 9.60  | 7.31  |
| 557-0201  | SE-F130     | 110°F | 130°F | 12.24 | 9.60  | 7.31  |
| 557-0202  | SE-L120     | 120°F | 106°F | 12.24 | 9.60  | 7.31  |
| 557-0203  | SE-L140     | 140°F | 100°F | 12.24 | 9.60  | 9.31  |
| 557-0204  | SE-L180     | 180°F | 140°F | 12.24 | 9.60  | 7.31  |
| 557-0205  | SE-L250     | 250°F | 210°F | 12.24 | 9.60  | 7.31  |
| 557-0206  | SES-110     | 110°F | 96°F  | 12.24 | 9.60  | 7.31  |
| 557-0208  | SES-L180    | 180°F | 150°F | 12.24 | 9.60  | 7.31  |
| 557-0207  | SES-L190    | 190°F | 160°F | 12.24 | 9.60  | 7.31  |
| 557-0209  | SES-L250    | 250°F | 220°F | 12.24 | 9.60  | 7.31  |