


2mm x 5mm Rectangular LED CBI® Circuit Board Indicator 12 LED Array

Dialight

566-xx08



PART NO

566-0208
566-0308
566-0408

COLOR

Green
Yellow
Red



Benefits

- 2mm x 5mm LED for low profile appearance
- Single PC board insertion of 12 LEDs
- Housing material meets UL94V-0
- Housing assures proper LED alignment
- Stand offs on housing facilitate PC board cleaning
- Vibration and shock resistant
- Black housing enhances contrast ratio

Custom Combinations

- For custom color combinations contact factory

LED Data

- For absolute maximum ratings and other optical/electrical data refer to the LED Data Sheets

Typical Operating Characteristics ($T_A=25^{\circ}\text{C}$)

See LED data sheet for additional information

Part Number	Color	Peak Wavelength nm	I_V mcd	V_F Volts	Test Current (mA)	Viewing Angle $2\theta_{1/2}$	LED Data sheet	Page #
566-0208	Green	565	4	2.2	20	110°	521-9332	5-15
566-0308	Yellow	583	3.5	2.1	20	110°	521-9452	5-15
566-0408	Red	635	7.4	2	20	140°	521-9499	5-15