


DRAMATICALLY INCREASED GRAPHICS PERFORMANCE

conga-BM67




- Up to Intel® Core™ i7-2710QE quad core processor
- Extreme graphics performance
- COM Express™ Type 2 module featuring DisplayPort and HDMI



Formfactor	COM Express™ Basic (95 x 125 mm) Type II Connector Layout						
CPU	Intel® Core™ i7-2710QE (SV)	2,1 GHz	32 nm process	6MB cache	1333 MHz	TDP 45 W	rPGA package
	Intel® Core™ i5 -2510E (SV)	2.5 GHz	32 nm process	3MB cache	1333 MHz	TDP 35 W	rPGA package
	Intel® Core™ i3-2330E	2.2 GHz	32 nm process	3MB cache	1333 MHz	TDP 35 W	rPGA package
	Intel® Celeron® B810	1.6 GHz	32 nm process	2MB cache		TDP 35 W	rPGA package
	Integrated dual channel memory controller up to 25,6 GByte/sec. memory bandwidth Integrated Intel® HD Graphics with dynamic frequency up to 1100 MHz Intel® Clear Video HD Technology						
DRAM	2 Sockets SO-DIMM DDR3 1333 MHz up to 16 GByte						
Chipset	Mobile Intel® 6 Series Chipset Intel® QM67 Platform Controller Hub						
Ethernet	Gigabit Ethernet Intel® Ethernet PHY with AMT support						
I/O Interfaces	6x PCI Express™ lanes 4x Serial ATA® (AHCI) with RAID support 1x EIDE (UDMA-66/100) optional 8x USB 2.0 (EHCI) PCI Bus 33 MHz Rev. 2.3 LPC bus I²C bus (fast mode 400 kHz multi-master)						
Sound	Digital High Definition Audio Interface with support for multiple audio codecs						
Graphics	Processor integrated Mobile Intel® 6 Series HD graphics OpenGL 3.0 and DirectX 10.1 support Two independent pipelines for full dual view support High performance hardware MPEG-2 decoding WMV9 (VC-1) and H.264 (AVC) support Blu-ray support @ 40 Mbit/s hardware motion compensation (using HDMI 1.4 with 3D) no PEG support						
LVDS (eDP optional)	Dual channel LVDS transmitter Supports flat panels 2x24 Bit interface VESA mappings resolutions up to 1920x1200 Automatic Panel Detection via EDID/EPI						
DisplayPort	3x DisplayPorts 1.1 max. resolution 2560x1600						
HDMI	3x ports shared						
CRT Interface	350 MHz RAMDAC resolutions up to QXGA (2048x1536)						
SDVO	1 x Intel compliant SDVO ports with 200MPixel/sec. Supports external DVI TV and LVDS transmitter						
congatec Board Controller	Multi Stage Watchdog non-volatile User Data Storage Manufacturing and Board Information Board Statistics BIOS Setup Data Backup I²C bus (fast mode 400 kHz multi-master) Power Loss Control						
Embedded BIOS Features	AMI Aptio® UEFI 2.x firmware 8 MByte serial SPI firmware flash						
Security	The conga-BM67 can be optionally equipped with a discrete "Trusted Platform Module" (TPM). It is capable of calculating efficient hash and RSA algorithms with key lengths up to 2,048 bits and includes a real random number generator. Security sensitive applications such as gaming and e-commerce will benefit also with improved authentication integrity and confidence levels.						
Power Management	ACPI 3.0 with battery support						
Operating Systems	Microsoft® Windows 8 Microsoft® Windows7 Microsoft® Windows® embedded Standard Microsoft® Windows XP Linux						
Power Consumption	Typ. application: Processor TDP: 35 .. 45 W see manual for full details						
Temperature	Operating: 0 .. +60°C Storage: -20 .. +80°C						
Humidity	Operating: 10 - 90% r. H. non cond. Storage: 5 - 95% r. H. non cond.						
Size	95 x 125 mm (3.74" x 4.92")						

conga-BM67 | Block diagram



conga-BM67 | Order Information

Article	PN	Description
conga-BM67/i7-2710QE	046101	Intel® Core™ i7-2710QE quad core processor with 2.1GHz 6MB L3 cache and 1600MT/s dual channel DDR3 memory interface
conga-BM67/i5-2510E	046102	Intel® Core™ i5-2510E dual core processor with 2.5GHz 3MB L3 cache and 1333MT/s dual channel DDR3 memory interface
conga-BM67/i3-2330E	046104	Intel® Core™ i3-2330E dual core processor with 2.2GHz 3MB L3 cache and 1333MT/s dual channel DDR3 memory interface
conga-BM67/B810	046105	Intel® Celeron® B810 dual core processor with 1.6GHz 2MB L3 cache and 1333MT/s dual channel DDR3 memory interface
conga-BM67/HSP-HP-B	046120	Standard heatspreader for high performance COM Express module conga-BM67 with integrated heat pipes. All standoffs are with 2.7mm bore hole
conga-BM67/HSP-HP-T	046121	Standard heatspreader for high performance COM Express module conga-BM67 with integrated heat pipes. All standoffs are M2.5mm thread
conga-BM67/CSP-HP-B	046122	Standard passive cooling solution for high performance COM Express module conga-BM67 with integrated heat pipes 15mm silver fins and 20mm overall heat sink height. All standoffs are with 2.7mm bore hole
conga-BM67/CSP-HP-T	046123	Standard passive cooling solution for high performance COM Express module conga-BM67 with integrated heat pipes 15mm silver fins and 20mm overall heat sink height. All standoffs are M2.5mm thread
conga-BM67/CSA-HP-B	046124	Standard active cooling solution for high performance COM Express module conga-BM67 with integrated heat pipes 15mm silver fins 20mm overall heat sink height and integrated 12V fan. All standoffs are with 2.7mm bore hole
conga-BM67/CSA-HP-T	046125	Standard active cooling solution for high performance COM Express module conga-BM67 with integrated heat pipes 15mm silver fins 20mm overall heat sink height and integrated 12V fan. All standoffs are M2.5mm thread
DDR3L-SODIMM-1600 (2GB)	068755	DDR3L SODIMM memory module with 1600 MT/s (PC3L-12800S) and 2GB RAM
DDR3L-SODIMM-1600 (4GB)	068756	DDR3L SODIMM memory module with 1600 MT/s (PC3L-12800S) and 4GB RAM
DDR3L-SODIMM-1600 (8GB)	068757	DDR3L SODIMM memory module with 1600 MT/s (PC3L-12800S) and 8GB RAM
Accessories		
conga-CEVAL	065749	Evaluation Carrier Board for COM Express Type 2 modules
conga-Cdebug	047854	COM-Express debugging platform. Including cable for COM PS/2 and VGA.
conga-LDVI/EPI	011115	LVDS to DVI converter board for digital flat panels with onboard EEPROM
conga-HDMI/Display Port adapter 4k	500030	The conga-DP/HDMI adapter 4k is used for evaluation of the DP/HDMI graphics interface of x86 Qseven and COM Express modules in combination with the congatec evaluation carrier boards conga-QEVAL and conga-TEVAL. It supports full 4k display resolution.
conga-FPA2	047250	Flatpanel prototype adapter to develop your own flatpanel adapter Including cables set.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[congatec:](#)

[conga-BM67/B810](#) [conga-BM67/i3-2330E](#) [conga-BM67/i5-2510E](#) [conga-BM67/i7-2710QE](#)