







|                                                                                       |          |          |                                                                                        |       |       |                                                                                                  |    |                                                                                          |              |
|---------------------------------------------------------------------------------------|----------|----------|----------------------------------------------------------------------------------------|-------|-------|--------------------------------------------------------------------------------------------------|----|------------------------------------------------------------------------------------------|--------------|
| www.fciconnect.com                                                                    |          |          | surface <input checked="" type="checkbox"/> tolerance std<br>ISO 1302 ISO 406 ISO 1101 |       |       | projection  |    | mm  |              |
| TOLERANCES UNLESS OTHERWISE SPECIFIED                                                 |          |          |                                                                                        |       |       |                                                                                                  |    |                                                                                          |              |
| Dr                                                                                    | M PESSON | 11/10/05 | ANGULAR                                                                                | 0.X   | ±0.3  | size                                                                                             | A2 | Scale                                                                                    |              |
| Eng                                                                                   | 11/10/05 | P LEGARE | LINEAR                                                                                 | 0.XX  | ±0.1  | ECN                                                                                              |    | LS07-0273                                                                                |              |
| Chr                                                                                   |          |          | 0° ±2°                                                                                 | 0.XXX | ±0.05 |                                                                                                  |    |                                                                                          |              |
| Appr                                                                                  |          |          | Product family                                                                         |       |       | - Spec ref                                                                                       |    |                                                                                          |              |
|  |          |          | SUB MALE DW EUROPE foot print                                                          |       |       | C01-8639-2319                                                                                    |    |                                                                                          | Rev.         |
|                                                                                       |          |          | full power right angle press fit                                                       |       |       |                                                                                                  |    |                                                                                          | C            |
| catalog no                                                                            |          |          | -                                                                                      |       |       | YY                                                                                               |    |                                                                                          | sheet 2 of 5 |



| PART NUMBER      | AMPS | MATINGS/<br>UNMATINGS | FRONT<br>ACCESSORY    | PCB<br>ACCESSORIES |
|------------------|------|-----------------------|-----------------------|--------------------|
| D*xWxP81C5A40LF  | 40   | 200                   | without               | without            |
| D*LxWxP81C5A40LF | 40   | 200                   | insert M3             | without            |
| D*OxWxP81C5A40LF | 40   | 200                   | insert UNC 4.40       | without            |
| D*VxWxP81C5A40LF | 40   | 200                   | female screw UNC 4.40 | without            |
| D*xWxP81C5M40LF  | 40   | 200                   | without               | metal bracket      |
| D*LxWxP81C5M40LF | 40   | 200                   | insert M3             | metal bracket      |
| D*OxWxP81C5M40LF | 40   | 200                   | insert UNC 4.40       | metal bracket      |
| D*VxWxP81C5M40LF | 40   | 200                   | female screw UNC 4.40 | metal bracket      |

shell size  
#  
E  
A  
A  
B  
C

LAYOUTS  
xWx  
2V2  
3V3  
3W3  
5W5  
8W8

| PART NUMBER      | AMPS | MATINGS/<br>UNMATINGS | FRONT<br>ACCESSORY    | PCB<br>ACCESSORIES |
|------------------|------|-----------------------|-----------------------|--------------------|
| D*xWxP81C6A40LF  | 40   | 500                   | without               | without            |
| D*LxWxP81C6A40LF | 40   | 500                   | insert M3             | without            |
| D*OxWxP81C6A40LF | 40   | 500                   | insert UNC 4.40       | without            |
| D*VxWxP81C6A40LF | 40   | 500                   | female screw UNC 4.40 | without            |
| D*xWxP81C6M40LF  | 40   | 500                   | without               | metal bracket      |
| D*LxWxP81C6M40LF | 40   | 500                   | insert M3             | metal bracket      |
| D*OxWxP81C6M40LF | 40   | 500                   | insert UNC 4.40       | metal bracket      |
| D*VxWxP81C6M40LF | 40   | 500                   | female screw UNC 4.40 | metal bracket      |



Copyright FCI.

|                                                                                       |          |           |                                                                                                                                          |       |                                                                                                  |               |                                                                                       |                  |           |
|---------------------------------------------------------------------------------------|----------|-----------|------------------------------------------------------------------------------------------------------------------------------------------|-------|--------------------------------------------------------------------------------------------------|---------------|---------------------------------------------------------------------------------------|------------------|-----------|
| www.fciconnect.com                                                                    |          |           | surface  tolerance std<br>ISO 1302 ISO 406 ISO 1101 |       | projection  |               |  |                  |           |
| TOLERANCES UNLESS OTHERWISE SPECIFIED                                                 |          |           |                                                                                                                                          |       |                                                                                                  |               |                                                                                       |                  |           |
| Dr                                                                                    | M PESSON | 11/10/05  | ANGULAR                                                                                                                                  | 0.X   | ±0.3                                                                                             | size<br>A2    | Scale<br>2:1                                                                          | ECN<br>LS07-0273 |           |
| Eng                                                                                   | 11/10/05 | P. LEGARE | LINEAR                                                                                                                                   | 0.XX  | ±0.1                                                                                             |               |                                                                                       |                  |           |
| Chr                                                                                   |          |           | 0° ±2°                                                                                                                                   | 0.XXX | ±0.05                                                                                            |               |                                                                                       |                  |           |
| Appr                                                                                  |          |           | Product family                                                                                                                           |       |                                                                                                  | - Spec ref    |                                                                                       |                  |           |
|  |          |           | SUB MALE DW EUROPE foot print                                                                                                            |       |                                                                                                  | deg no        |                                                                                       |                  | Rev.<br>C |
|                                                                                       |          |           | full power right angle press fit                                                                                                         |       |                                                                                                  | C01-8639-2319 |                                                                                       |                  |           |
| catalog no                                                                            |          |           | -                                                                                                                                        |       |                                                                                                  | YY            |                                                                                       | sheet 3 of 5     |           |

