




1. MAXIMUM INSERTION LOSS PER CONNECTOR MATED TO REFERENCE LEAD: 0.50 dB + 1.5 dB/km, SEE TABLE.
2. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702.

0.65	100.00±1.00	[3937.0±39.4]	8-6754399-1
0.62	80.00±0.80	[3149.6±31.5]	8-6754399-0
0.56	40.00±0.40	[1574.8±15.7]	4-6754399-0
0.55	30.00±0.30	[1181.1±11.8]	3-6754399-0
0.54	25.00±0.30	[984.2±11.8]	2-6754399-5
0.53	24.00±0.30	[944.9±11.8]	2-6754399-4
0.53	23.00±0.30	[905.5±11.8]	2-6754399-3
0.53	22.00±0.30	[866.1±11.8]	2-6754399-2
0.53	21.00±0.30	[826.8±11.8]	2-6754399-1
0.53	20.00±0.30	[787.4±11.8]	2-6754399-0
0.53	18.00±0.30	[708.7±11.8]	1-6754399-8
0.52	16.00±0.30	[629.9±11.8]	1-6754399-6
0.52	15.00±0.15	[590.5±5.9]	1-6754399-5
0.52	14.00±0.15	[551.2±5.9]	1-6754399-4
0.52	13.00±0.15	[511.8±5.9]	1-6754399-3
0.52	12.00±0.15	[472.4±5.9]	1-6754399-2
0.52	11.00±0.15	[433.1±5.9]	1-6754399-1
0.52	10.00±0.15	[393.7±5.9]	1-6754399-0
0.51	9.00±0.15	[354.3±5.9]	6754399-9
0.51	8.00±0.15	[315.0±5.9]	6754399-8
0.51	7.00±0.08	[275.6±3.1]	6754399-7
0.51	6.00±0.08	[236.2±3.1]	6754399-6
0.51	5.00±0.08	[196.8±3.1]	6754399-5
0.50	4.00±0.08	[157.5±3.1]	6754399-4
0.50	3.00±0.05	[118.1±2.0]	6754399-3
0.50	2.00±0.05	[78.7±2.0]	6754399-2
0.50	1.00±0.05	[39.4±2.0]	6754399-1
INSERTION LOSS (dB)	L METERS [INCHES]		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

J BARRY

17FEB09

CHK

J BARRY

17FEB09

APVD

J BARRY

17FEB09

DIMENSIONS:

METERS [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

MATERIAL

-

WEIGHT

-

CUSTOMER DRAWING

Tyco Electronics

Tyco Electronics Corporation

Harrisburg, PA 17105-3608

NAME

CABLE ASSEMBLY, FIBER OPTIC, 50/125um (XG) ZIPCORD, LC DUPLEX TO LC DUPLEX

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

6754399

-

SCALE

NTS

SHEET

1 OF 1

REV

A1

AMP 1471-9 REV 31MAR2000