

Data Sheet

**Intelligent pH Meter
w/ Probe**

Model 760KIT

- pH meter with mV measurement
- RS-232 PC Interface
- Plug and Play function
- pH Probe

pH Probe

Applications	High quality, Professional, laboratory & field usage.
Measuring Range	0 to 14 pH
Measuring Temp	0 to 100°C (32° to 100° F)
Electrode Structure	Combination type.
Zero Potential for pH Value	71 pH
Body Material	Epoxy
Connector	BNC
Mechanical Protection	With protection bottle on the electrode head
Dimensions	Body Length - 120 mm Body Dia - 9.5 mm Cable Length - 750 mm

pH meter

Measurement	Range	Resolution	Accuracy
pH	0 to 14 pH	0.01 pH	± (0.02 PH + 2 dgt)
mV	0 to 1999 mV	1 mV	± (0.5% + 2 dgt)

- * pH accuracy is based on calibrated meter only.
- * Specification tests under the environment RF Field Strength less than V/M & frequency less than 30 MHz only.

