

THIS DRAWING IS UNPUBLISHED.										RELEASED FOR PUBLICATION SEP ,2005.										LOC		DIST		REVISIONS																	
COPYRIGHT 2005 By -										ALL RIGHTS RESERVED.														変更		DATE		DWN		APVD											
																								DESCRIPTION																	
																								REVISED PER ECR-11-006365		28MAR2011		A.L		S.Y											
1 CONTACT COPLANALITY IS 0.1 MAX. THIS DIMENSION MEANS CENTER OF THE POCKET. M3 TAPPING + BVTP RECOMMENDED TORQUE: 68.6N (7Kgf) MAX. FINISH CONTACT: V μm MIN. Au PL. ON CONTACT AREA (V: SEE TABLE) 0.03~0.1 μm Au PL. ON TERMINAL AREA Ni UNDER PL. ALL OVER SHELL: Sn PL. (MATTE) ALL OVER Ni UNDER PL. ALL OVER SCREW SIZE QTY PRINT ON THE LABEL. (EMBOSS PACKING)										1 コンタクトコプラナリティーは 0.1 以下。 本寸法はポケットの中心を表す。 M3 TAPPING + BVTP 推奨トルク: 68.6N (7Kgf) 以下。 仕上 コンタクト: コンタクトエリアに V μm 以上の 金めっき (V: 表参照) ターミナルエリアに 0.03~0.1 μm の金めっき ニッケル下地めっきを施す シェル: すずめっき (つや消し) ニッケル下地めっきを施す スクリューサイズ 数量はラベルに印字される (EMBOSS 梱包)																															
0.3	-	70	1.9	-	-	-	-	33.5	37.5	9.32	0.4	32	28.4	14.2	16	WITHOUT TAPE	WITHOUT FLANGE	THROUGH HOLE	(SEE SHEET 2)	SOFT TRAY (SEE SHEET 11)	6-1903015-3																				
0.76	M3 x 0.5	70	1.9	46	138	6-23	46	-	-	-	-	-	-	-	-	WITH TAPE	WITH FLANGE	THROUGH HOLE	(SEE SHEET 3)	SOFT TRAY (SEE SHEET 7)	9-1903015-4																				
0.3	M3 x 0.5	200	1.9	-	-	-	-	45.5	49.5	18.3	0.5	44	40.4	20.2	20	WITH TAPE	WITH FLANGE	THROUGH HOLE	(SEE SHEET 3)	EMBOSS (SEE SHEET 6)	9-1903015-3																				
0.3	M3 x 0.5	70	1.9	-	-	-	-	-	-	-	-	-	-	-	-	WITHOUT TAPE	WITH FLANGE	THROUGH HOLE	(SEE SHEET 3)	SOFT TRAY (SEE SHEET 10)	8-1903015-4																				
0.1	-	550	1.9	-	-	-	-	33.5	37.5	9.32	0.4	32	28.4	14.2	16	WITHOUT TAPE	WITHOUT FLANGE	THROUGH HOLE	(SEE SHEET 2)	EMBOSS (SEE SHEET 6)	7-1903015-1																				
0.3	M3 x 0.5	200	1.9	-	-	-	-	45.5	49.5	18.3	0.5	44	40.4	20.2	20	WITHOUT TAPE	WITH FLANGE	FULL SMT	(SEE SHEET 5)	EMBOSS (SEE SHEET 6)	5-1903015-9																				
0.3	-	550	0.8	-	-	-	-	33.5	37.5	9.32	0.4	32	28.4	14.2	16	WITHOUT TAPE	WITHOUT FLANGE	THROUGH HOLE	(SEE SHEET 2)	EMBOSS (SEE SHEET 6)	5-1903015-5																				
0.3	M3 x 0.5	70	1.9	46	138	6-23	46	-	-	-	-	-	-	-	-	WITHOUT TAPE	WITH FLANGE	THROUGH HOLE	(SEE SHEET 3)	SOFT TRAY (SEE SHEET 7)	5-1903015-4																				
0.3	M3 x 0.5	200	1.9	-	-	-	-	45.5	49.5	18.3	0.5	44	40.4	20.2	20	WITHOUT TAPE	WITH FLANGE	THROUGH HOLE	(SEE SHEET 3)	EMBOSS (SEE SHEET 6)	5-1903015-3																				
0.3	φ2.65±0.3	70	1.9	46	138	6-23	46	-	-	-	-	-	-	-	-	WITHOUT TAPE	WITH FLANGE	THROUGH HOLE	(SEE SHEET 3)	SOFT TRAY (SEE SHEET 7)	5-1903015-2																				
0.3	-	400	1.9	-	-	-	-	33.5	37.5	9.32	0.4	32	28.4	14.2	16	WITHOUT TAPE	WITHOUT FLANGE	THROUGH HOLE	(SEE SHEET 2)	EMBOSS (SEE SHEET 6)	5-1903015-1																				
0.3	M3 x 0.5	70	1.0	46	138	6-23	46	-	-	-	-	-	-	-	-	WITHOUT TAPE	WITH FLANGE	THROUGH HOLE	(SEE SHEET 3)	SOFT TRAY (SEE SHEET 7)	4-1903015-1																				
0.76	-	400	1.2	-	-	-	-	33.5	37.5	9.32	0.4	32	28.4	14.2	16	WITHOUT TAPE	WITHOUT FLANGE	THROUGH HOLE	(SEE SHEET 2)	EMBOSS (SEE SHEET 6)	2-1903015-2																				
0.76	M3 x 0.5	70	1.9	-	-	-	-	-	-	-	-	-	-	-	-	WITHOUT TAPE	WITH FLANGE	THROUGH HOLE	(SEE SHEET 3)	SOFT TRAY (SEE SHEET 9)	1903015-8																				
0.76	φ2.65±0.3	70	1.9	-	-	-	-	-	-	-	-	-	-	-	-	WITHOUT TAPE	WITH FLANGE	THROUGH HOLE	(SEE SHEET 3)	SOFT TRAY (SEE SHEET 9)	1903015-7																				
0.76	M3 x 0.5	50	1.9	54.4	120	4-30	54.4	-	-	-	-	-	-	-	-	WITHOUT TAPE	WITH FLANGE	THROUGH HOLE	(SEE SHEET 3)	SOFT TRAY (SEE SHEET 9)	1903015-5																				
0.76	M3 x 0.5	70	1.9	46	138	6-23	46	-	-	-	-	-	-	-	-	WITHOUT TAPE	WITH FLANGE	THROUGH HOLE	(SEE SHEET 4)	SOFT TRAY (SEE SHEET 8)	1903015-4																				
0.76	M3 x 0.5	200	1.9	-	-	-	-	45.5	49.5	18.3	0.5	44	40.4	20.2	20	WITHOUT TAPE	WITH FLANGE	THROUGH HOLE	(SEE SHEET 4)	EMBOSS (SEE SHEET 6)	1903015-3																				
0.76	φ2.65±0.3	70	1.9	46	138	6-23	46	-	-	-	-	-	-	-	-	WITHOUT TAPE	WITH FLANGE	THROUGH HOLE	(SEE SHEET 3)	SOFT TRAY (SEE SHEET 7)	1903015-2																				
0.76	-	400	1.9	-	-	-	-	33.5	37.5	9.32	0.4	32	28.4	14.2	16	WITHOUT TAPE	WITHOUT FLANGE	THROUGH HOLE	(SEE SHEET 2)	EMBOSS (SEE SHEET 6)	1903015-1																				
V	U	T	AA	S	R	P	N	M	L	K	J	H	G	F	E	POLYIMIDE TAPE	FLANGE	SHELL TYPE	CONNECTOR	PACKING	PART NUMBER																				
Au PL.	SCREW SIZE	QTY	DIMENSION													PART LIST																									
THIS DRAWING IS A CONTROLLED DOCUMENT.																DWN R.MURAYAMA 26SEP2005		TE Connectivity																							
DIMENSIONS: 単位: 概 mm																CHK T.KIMURA 26SEP2005		NAME 名称																							
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差																APVD T.KIMURA 26SEP2005		HDMI 19 POS RECEPTACLE ASSY SMT SHORT TYPE																							
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±																PRODUCT SPEC 108-78180-2		SIZE CAGE CODE DRAWING NO 番号																							
MATERIAL 材料																APPLICATION SPEC 取付適用規格		A3 00779 C=1903015																							
FINISH 仕上																WEIGHT		RESTRICTED TO																							
CUSTOMER DRAWING																SCALE 4:1		SHEET 1 OF 12 REV R																							

4

3

2

1

THIS DRAWING IS UNPUBLISHED.



RELEASED FOR PUBLICATION

SEP, 2005.




© COPYRIGHT 2005 By -

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			DATE	DWN	APVD
		P	LTR	DESCRIPTION			
-	-	-	-	SEE SHEET 1	-	-	-




PANEL CUT OUT DIMENSION (REFERENCE)



P.C.B LAYOUT (REFERENCE)
SHOWN AS CONNECTOR MOUNTING SIDE
TOLERANCE: NON-CUMULATIVE

BRASS	CONTACT	(3)
PHOSPHOR BRONZE	SHELL	(2)
GLASS FILLED LCP UL94V-0, BLACK COLOR	HOUSING	(1)
MATERIAL	DESCRIPTION	ITEM

CONNECTOR: WITHOUT FLANGE THROUGH HOLE TYPE



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN				TE Connectivity HDMI 19 POS RECEPTACLE ASSY SMT SHORT TYPE	
DIMENSIONS: 單位: 毫米 mm		CHK					
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD					
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		NAME 名稱					
MATERIAL 材料		FINISH 仕上		PRODUCT SPEC 製品規格		SIZE	
				APPLICATION SPEC 取付適用規格		CAGE CODE	
				WEIGHT		DRAWING NO 番号	
				CUSTOMER DRAWING		A3 00779 C=1903015	
						RESTRICTED TO	
						SCALE 4:1	
						SHEET 2 OF 12	
						REV R	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

SEP, 2005.

© COPYRIGHT 2005 By -

ALL RIGHTS RESERVED.

LOC
DIST

REVISIONS

變更

DESCRIPTION

DATE

DWN

APVD

P



LTR

SEE SHEET 1




-

-

-



PANEL CUT OUT DIMENSION (REFERENCE)



P.C.B LAYOUT (REFERENCE)
SHOWN AS CONNECTOR MOUNTING SIDE
TOLERANCE: NON-CUMULATIVE

POLYIMIDE	TAPE	(4)
BRASS	CONTACT	(3)
PHOSPHOR BRONZE	SHELL	(2)
GLASS FILLED LCP UL94V-0, BLACK COLOR	HOUSING	(1)
MATERIAL	DESCRIPTION	ITEM

CONNECTOR: WITH FLANGE THROUGH HOLE TYPE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

單位: 毫米

mm

TOLERANCES UNLESS

OTHERWISE SPECIFIED:

一般公差

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

FINISH 仕上

MATERIAL 材料

DWN

CHK

APVD

PRODUCT SPEC

製品規格

APPLICATION SPEC

取付適用規格

WEIGHT

CUSTOMER DRAWING

TE

TE Connectivity

HDMI 19 POS RECEPTACLE ASSY
SMT SHORT TYPE

SIZE

CAGE CODE

DRAWING NO

書号

RESTRICTED TO

A3

00779

C=1903015

SCALE

尺度 4:1

SHEET

3 OF 12

REV

R

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

SEP, 2005.

© COPYRIGHT 2005 By --

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

変更

DESCRIPTION

DATE

DWN

APVD

P



LTR

SEE SHEET 1




-

-

-




PANEL CUT OUT DIMENSION (REFERENCE)


P.C.B LAYOUT (REFERENCE)
SHOWN AS CONNECTOR MOUNTING SIDE
TOLERANCE: NON-CUMULATIVE

CONNECTOR: WITH FLANGE FULL SMT TYPE

BRASS	CONTACT	(3)
PHOSPHOR BRONZE	SHELL	(2)
GLASS FILLED LCP UL94V-0, BLACK COLOR	HOUSING	(1)
MATERIAL	DESCRIPTION	ITEM



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 話
mmMATERIAL
材料TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±FINISH
仕上

DWN

CHK

APVD

PRODUCT SPEC
製品規格APPLICATION SPEC
取付適用規格

WEIGHT

CUSTOMER DRAWING

NAME
名称

TE Connectivity

HDMI 19 POS RECEPTACLE ASSY
SMT SHORT TYPE

SIZE

CAGE CODE

DRAWING NO
番号

A3

00779

C=1903015

RESTRICTED TO

SCALE
尺度

4:1

SHEET

5 OF 12

REV

R

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

SEP, 2005.



© COPYRIGHT 2005 By --

ALL RIGHTS RESERVED.


1903015-1, 2-1903015-2, 5-1903015-1

5-1903015-5, 7-1903015-1; AS SHOWN

LOC	DIST	REVISIONS			DATE	DWN	APVD
		P	LTR	DESCRIPTION			
				SEE SHEET 1			



B-B



SEE DETAIL A


WEEDING THE COVER TAPE: 300 MIN
(NOT INCLUDE EMPTINESS POCKET)PEELING ANGLE: 165°~180°
PEELING STRENGTH:
0.1~0.7N (300mm/min.)

PLASTIC REEL


PULL OUT DIRECTION

CARRIER TAPE


LABEL

400 MIN. WITH PRODUCT CHARGE 25 HOLES MIN.
QTY: T PCS5-1903015-3; AS SHOWN
(SCALE 1:1)


DETAIL A




B-B

5-1903015-9; AS SHOWN
(SCALE 1:1)


DETAIL A




B-B

9-1903015-3; AS SHOWN
(SCALE 1:1)


DETAIL A



B-B

1903015-3; AS SHOWN
(SCALE 1:1)

DETAIL A



B-B



LABEL DESCRIPTION

TYCO P/N: *-1903015-*
QTY: * pcs
D/C: MADE IN CHINA

PET	COVER TAPE
PS	CARRIER TAPE
PLASTIC	REEL
MATERIAL	DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
單位: 毫米TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±FINISH
仕上MATERIAL
材料

DWN

CHK

APVD

PRODUCT SPEC
製品規格APPLICATION SPEC
取付適用規格

WEIGHT

CUSTOMER DRAWING

TE

TE Connectivity

HDMI 19 POS RECEPTACLE ASSY
SMT SHORT TYPE

SIZE

CAGE CODE

DRAWING NO

A3

00779

C=1903015

RESTRICTED TO

SCALE
尺度 4:1

SHEET

6 OF 12

REV
R


LOC	DIST
—	—

變更

DWN

SEE SHEET 1

	-



	DWN
--	-----

CHK

APVD

PRODUCT SPEC


APPLICATION S

取付適用規格

WEIGHT

CUSTOMER DRAWING

DIMENSIONS
單位：耗
mm



MATERIAL 材料	
----------------	--

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0	PLC	$\pm$
1	PLC	$\pm$
2	PLC	$\pm$
3	PLC	$\pm$
4	PLC	$\pm$
ANGLES		

FINISH
仕上



TE Connectivity

PS
MATERIAL

TRAY	DESCRIPTION

HDMI 19 POS RECEPTACLE ASSY
SMT SHORT TYPE

SIZE	A3
------	----

CAGE CODE	00779
-----------	-------

DRAWING NO
番号
C-1903015

RESTRICTED



SCALE
比例 4:1

SHEET 7 OF 12


REV	R
-----	---

1903015-4; AS SHOWN

LOC —	DIST —	REVISIONS 変更					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—




DETAIL C
(SCALE 2:1)



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS
單位：耗
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
一般公差



MATERIAL 材料	
----------------	--

ANGLES
FINISH 仕上

	DWN
--	-----

CHK

APV

PRODUCT SPEC
製品規格

APPLICATION SPEC
取付適用規格

WEIGHT	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40	41	42	43	44	45	46	47	48	49	50	51	52	53	54	55	56	57	58	59	60	61	62	63	64	65	66	67	68	69	70	71	72	73	74	75	76	77	78	79	80	81	82	83	84	85	86	87	88	89	90	91	92	93	94	95	96	97	98	99	100
1	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40	41	42	43	44	45	46	47	48	49	50	51	52	53	54	55	56	57	58	59	60	61	62	63	64	65	66	67	68	69	70	71	72	73	74	75	76	77	78	79	80	81	82	83	84	85	86	87	88	89	90	91	92	93	94	95	96	97	98	99	100

CUSTOMER DRAWING

NAME 名称	UNIT 单位	QTY 数量	PRICE 单价	TOTAL 合计
1	1	1	1	1

SIZE	
------	--

CAGE CODE

DRAWING NO
番号

A300779C-1903015

RESTRICTED TO

12	REV	
----	-----	--



TE Connectivity





PS
MATERIAL

TRAY
DESCRIPTION

HDMI 19 POS RECEPTACLE ASSY
SMT SHORT TYPE

1903015-7, 1903015-8; AS SHOWN

LOC	DIST	REVISIONS				DATE	DWN	APVD
		P	LTR	変更	DESCRIPTION			
-	-	-	-	SEE SHEET 1		-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		TE Connectivity			
		CHK					
DIMENSIONS: 単位： 純 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD		NAME 名称	
		0 PLC ±		PRODUCT SPEC 製品規格		HDMI 19 POS RECEPTACLE ASSY SMT SHORT TYPE	
		1 PLC ±					
		2 PLC ±					
		3 PLC ±		APPLICATION SPEC 取付適用規格			
		4 PLC ±		WEIGHT			
MATERIAL 材料		FINISH 仕上		SIZE		CAGE CODE	
				DRAWING NO 番号		RESTRICTED TO	
				A3		00779	
				C=1903015		—	
CUSTOMER DRAWING				SCALE 尺度 4:1		SHEET 9 of 12	
				REV R			

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

SEP, 2005.

© COPYRIGHT 2005 By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

変更

DESCRIPTION

DATE

DWN

APVD

P

LTR

SEE SHEET 1

8-1903015-4; AS SHOWN

D

D

C


C

B


B

A

A




TRAY A




TRAY B

TRAY B (EMPTY)




TRAY B

TRAY A

Y-Y
(SCALE 2:1)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 話
mmMATERIAL
材料TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±FINISH
仕上

DWN

CHK

APVD

PRODUCT SPEC
製品規格APPLICATION SPEC
取付適用規格

WEIGHT

CUSTOMER DRAWING

NAME
名称

TE Connectivity

HDMI 19 POS RECEPTACLE ASSY
SMT SHORT TYPE

SIZE

CAGE CODE

DRAWING NO
番号

A3

00779

C=1903015

RESTRICTED TO

SCALE
尺度 4:1

SHEET

10 OF 12

REV

R

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

SEP ,2005.

© COPYRIGHT 2005 By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

変更

DESCRIPTION

DATE

DWN

APVD

P

LTR

SEE SHEET 1

-

-

-

PLUG CONNECTOR

RECEPTACLE
CONNECTOR
WITHOUT FLANGE TYPE

2 MAX

1.6 REF

2 MIN

SCREW

PLUG CONNECTOR

RECEPTACLE
CONNECTOR
WITH FLANGE TYPE

2 MAX

MAX
ø6

1.6 REF

2 MIN

MATING CONDITION (REFERENCE)
(SCALE 2:1)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC


製品規格

APPLICATION SPEC

取付適用規格

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:
単位: 話
mmMATERIAL
材料TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±FINISH
仕上

TE Connectivity

HDMI 19 POS RECEPTACLE ASSY
SMT SHORT TYPE

SIZE

CAGE CODE

DRAWING NO

番号

A3

00779

C=1903015

RESTRICTED TO

SCALE
尺度 4:1







SHEET

11 OF 12

REV

R

P/N:6-1903015-3



PS	TRAY
MATERIAL	DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		TE Connectivity							
		CHK									
DIMENSIONS: 單位: 毫米		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD		NAME 名稱					
		0 PLC ±		PRODUCT SPEC 製品規格		HDMI 19 POS RECEPTACLE ASSY SMT SHORT TYPE					
		1 PLC ±									
		2 PLC ±									
		3 PLC ±									
		4 PLC ±		APPLICATION SPEC 取付適用規格							
		4 ANGLES ±		WEIGHT		SIZE		CAGE CODE	DRAWING NO 番号	RESTRICTED TO	
MATERIAL 材料		FINISH 仕上		A3		00779		C=1903015		—	
CUSTOMER DRAWING						SCALE 尺度		4:1		SHEET 12 of 12	REV R