




2.03-3.05 DIA [.080-.120] DIA	[#22-#18] AWG	0.46±0.025 [.018±.001]	63242-1
INSULATION RANGE	WIRE SIZE	MATING TAB THICKNESS	PART NO
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.38 [.015] 3 PLC DEC ± - ANGLES ± -	DR 5/16/95 JR RUTH CHK 5/16/95 MS FEHER APPD 5/16/95 P DESANTIS APPD 5/16/95 R REINER PRODUCT SPEC -	AMP AMP Incorporated Harrisburg, PA 17105-3608	
MATERIAL H04 BRASS	FINISH -	NAME RECEPTACLE, FASTON, PIGGYBACK, 2.79 [.110] SERIES	
THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		SIZE B	CAGE CODE 00779
		SCALE 5:1	DRAWING NO C-63242
		WEIGHT -	SHEET 1 OF 1