



main menue



- home
- test & measurement
- products
- skills
- download

online catalogue T&M

- clamp-type test probes
- crocodile clips
- test probes
- oscilloscope test probes
- measuring leads
- plugs
- sockets
 - 2 mm system
 - 2 mm safety system
 - 4 mm system
 - 4 mm safety system
- sets
- miscellaneous
- company
 - portrait
 - corporate association
 - location maps
 - fairs and exhibitions
 - jobs
 - imprint
 - terms and conditions

Home > sockets > sockets > PKI 100

PKI 100

datasheet for PKI 100
article number: 930757104



View Full-Size Image



search online catalogue

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code



product description:		order number: 930 757-104	
description:		Pole terminal with captive insulated head, which is held under constant pressure against the insulated rings by a spring. 4 mm diameter nickel-plated, brass threaded bolt with 2 mm diameter transverse hole. For non-rotating installation in switchpanels and equipment chassis with wall thickness up to 3.5 mm.	
typ:		PKI 100 gruen/green	
system:		4mm system	
order number:		930 757-104	
color			
other color versions:			
technical data			
measurement category acc. to IEC 61010:		CAT I	
type of contact:		4 mm socket (unsprung), 2 mm cross hole	
type of termination:		M4 thread	
rated voltage:		30 VAC / 60 VDC	
rated current:		35 A	
Please consider derating curve!			
contact resistance:		2 mOhm	
mounting:		screw	
material			
contact material:		brass	
contact surface material:		nickel	
housing material:		PA	
environmental conditions:			
temperature range:		-25 °C to +100 °C	
inflammable class:			
housing (basic material):		UL 94 V - 2	
drawing			
			