


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		C	ECR-05-017969	12JAN06	JMS	FWK

NOTES:

- 1 PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2 100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3 Au PLATING
- 4 ELECTRICAL CHARACTERISTICS
FREQUENCY RANGE: DC - 4 GHz
NOMINAL IMPEDANCE: 50 Ohm
INSULATION RESISTANCE: 1000 MOhm
WORKING VOLTAGE: 250 Volts RMS at Sea Level
DIELECTRIC WITHSTAND VOLTAGE: 750 Volts RMS Max
CONTACT RESISTANCE:
CENTRE CONTACT: 6.00 mOhm Max
OUTER CONTACT: 1.00 mOhm Max
- 5 MECHANICAL CHARACTERISTICS
MOUNT NUT RECOMMENDED TORQUE: 0.75N
DURABILITY: 500 Cycles Min
- 6 ENVIRONMENTAL CHARACTERISTICS
OPERATING TEMPERATURE: -65 to +165 DegC



		1	1	BRASS	⚠	HEX NUT	5
		1	1	BRASS	⚠	LOCKWASHER	4
		1	1	BRASS	⚠	CONTACT	3
		1	1	PTFE		INSULATION	2
		1	1	BRASS	⚠	BODY	1
		6--0	1--0	MATERIAL		DESCRIPTION	ITEM
		⚠	⚠				
QUANTITY PER ASSY				PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.SANDWELL	12JAN06	tyco		Tyco Electronics Corporation			
		CHK S.PARLOW	12JAN06	Electronics		Bideford EX39 4HE			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD F.WHEELER-KING	12JAN06	NAME			
				PRODUCT SPEC	SMB BULKHEAD SOCKET FRONT MOUNT 50 OHM				
				—	—				
				APPLICATION SPEC	—				
				—					
MATERIAL SEE TABLE	FINISH —	WEIGHT —		SIZE A3	CAGE CODE 00779	DRAWING NO C-1337480		RESTRICTED TO —	
CUSTOMER DRAWING						SCALE NTS	SHEET 1	OF 1	REV C