




General ordering data

Order No.	1784180000
Part designation	DLD 2.5 DB
Version	Initiator/actuator terminal, 2.5 mm ² , Screw connection, Wemid, dark beige, TS 35
EAN	4032248189854
Qty.	50 pc(s).

Product notes

Note, ordering data	Blue version order No. 6269250000 (50 pcs)
Note, technical data	Rated voltage is reduced to 30 V AC when one pole with a different potential is skipped with a cross-connector.
Product description	Time- and space-saving wiring for initiators and actuators. All the connections for initiator and actuator are in one terminal.
Note, accessories	Insulation plate TSCH 1 order No. 0319160000 (100 pcs) Partial end plate TEAP DLD2.5/PE DB order No. 1783810000 (20 pcs)

2 clampable conductors (H05V/H07V) with equal cross-section (rated connection)

Solid, min.	0.5 mm ²
Solid, max.	1.5 mm ²
Flexible, min.	0.5 mm ²
Flexible, max.	1.5 mm ²
Flexible with ferrule, min. (DIN 46228 pt 1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228 pt 1)	1.5 mm ²

Additional technical data

Colour of insulating material	dark beige
Connection direction	on side
End plate required	Yes
Explosion-tested version "Ex e"	No
Installation advice	TS 35

Additional technical data

Insulating material	Wemid
Levels cross-connected internally	No
No. of identical terminals	1
No. of levels	3
No. of terminal strips per level	2
Open sides	right
Operating temperature range	- 50 °C, + 120 °C
Product family	W-Series
Type of connection	Screwed
Type of mounting	Snap-on
UL 94 flammability rating of insulation material	V-0
Version	Feed-through terminal with electronic components

CSA rating data

Voltage (CSA)	300 V
CSA current	10 A
Min. cross-section (CSA)	AWG 26
Max. cross-section (CSA)	AWG 12

Conductors for clamping (additional connection)

Type of connection	Screw connection
Flexible with ferrule, min. (DIN 46228 pt 1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228 pt 1)	2.5 mm ²

Conductors for clamping (rated connection)

Clamping range, min.	0.13 mm ²
Clamping range, max.	4 mm ²
Type of connection	Screw connection
2nd type of connection	screwed
Connection direction	on side
No. of connections	6
Stripping length	7 mm
Clamping screw	M 2.5
Blade size	0.6 x 3.5 mm
Tightening torque range	0.4...0.6 Nm
Torque level with DMS electric screwdriver	1
Gauge to IEC 60947-1	A3
Solid, min.	0.5 mm ²
Solid, max.	4 mm ²
Stranded, min.	1.5 mm ²
Stranded, max.	4 mm ²
Flexible, min.	0.5 mm ²
Flexible, max.	4 mm ²
Flexible with ferrule, min. (DIN 46228/1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228/1)	2.5 mm ²
AWG conductor size, min.	AWG 26
AWG conductor size, max.	AWG 12
AWG conductor size, min.	0.13 mm ²
AWG conductor size, max.	3.31 mm ²

Dimensions

Width	6.1 mm
Height of lowest version	49 mm
Length	82.5 mm
TS 35 offset	36.5 mm

Disconnect terminals

Torque level with DMS electric screwdriver	1
--	---

Rating data

Rated cross-section	2.5 mm ²
Rated voltage	250 V
Rated impulse voltage	4 kV
Rated current	24 A
Standards	IEC 60947-7-1
Current with max. conductor	24 A
Pollution severity	3

UL rating data

Voltage (UL)	300 V
Current (UL)	10 A
Min. cross-section (UL)	AWG 22
Max. cross-section (UL)	AWG 12

Approvals

Approvals institutes



Classifications

ETIM 2.0	EC000900
ETIM 3.0	EC000900
eClass 4.1	27-14-11-28
eClass 5.0	27-14-11-28
eClass 5.1	27-14-11-28

Similar products

Order No.	Part designation	Version
1783790000	DLD 2.5/PE DB	Initiator/actuator terminal, 2.5 mm ² , Screw connection, Wemid, dark beige, TS 35