


samtec

HLS-0308-G-2



CARRIER STRIPS HLS & HLT SERIES

Mates with:

TS-1, HTS, BBS, BBL,
BHS, BBD, BDL, LBS,
HLT, TSB

Lead sockets "float" and
"self-center" when this
low profile carrier is
soldered. Ideal for most
VP or IR processes.

SPECIFICATIONS

For complete specifications
see www.samtec.com?HLS

Same as SL-1 except:
Insulator Material:
Black High
Temperature Thermoplastic
Temperature Range:
-55°C to +140°C
Heat Deflection Temp:
215°C @ 264 psi

Note:

This Series is non-standard,
non-returnable.

HLS	NO. ROWS	NO. PINS PER ROW	PLATING OPTION	LEAD STYLE	OPTION
Total Pins = No. Rows x No. Pins Per Row		-01 thru -20 (requires both digits)	-G = 30μ" (0,76μm) Gold Contact 10μ" (0,25μm) Gold Shell		-L = Locking Socket
			-T = 30μ" (0,76μm) Gold Contact, Tin Shell		
			-S = 10μ" (0,25μm) Gold Contact, Tin Shell (Styles 2 & 22 only)		
			-TT = Tin Contact and Shell (Styles 2, 10, 11, 12, 18, 22, 30, 31 & 32 only)		

Low Insertion Force (LIF) Available

-2 or -18 = Standard Socket For LIF specify -22 or -38 <table> <tr> <th>STYLE</th><th>Y</th><th>Z</th></tr> <tr> <td>-2 or -22</td><td>(3,18) .125</td><td>(7,62) .300</td></tr> <tr> <td>-18 or -38</td><td>(4,57) .180</td><td>(8,89) .350</td></tr> </table> Lead DIA Accepted = .015" to .022" Insertion Depth = .095" to .150" Style 2 Component Part No. = SC-1P1 Style 22 Component Part No. = EZ-1P1 Style 18 Component Part No. = SC-6P1 Style 38 Component Part No. = EZ-6P1	STYLE	Y	Z	-2 or -22	(3,18) .125	(7,62) .300	-18 or -38	(4,57) .180	(8,89) .350	-3 = Body Only For LIF specify -23 Lead DIA Accepted = .015" to .022" Insertion Depth = .125" to .175" Style 3 Component Part No. = SC-1S1 Style 23 Component Part No. = EZ-1S1	-10 = Low Profile Hollow Leg For LIF specify -30 Lead DIA Accepted = .015" to .020" Insertion Depth = .105" to .170" Style 10 Component Part No. = SC-3P1 Style 30 Component Part No. = EZ-3P1	-11 = Low Profile Standard For LIF specify -31 Lead DIA Accepted = .016" to .021" Insertion Depth = .080" to .115" Style 11 Component Part No. = SC-4P1 Style 31 Component Part No. = EZ-4P1	-12 = Micro Socket For LIF specify -32 Lead DIA Accepted = .016" to .020" Insertion Depth = .080" to .150" Style 12 Component Part No. = SC-5P1 Style 32 Component Part No. = EZ-5P1	-14 or -15 = Short Tail <table> <tr> <th>STYLE</th><th>Z</th></tr> <tr> <td>-14</td><td>(5,08) .200</td></tr> <tr> <td>-15</td><td>(4,24) .167</td></tr> </table> N/A Single Row Lead DIA Accepted = .015" to .022" Style 14 Insertion Depth = .125" to .150" Style 14 Component Part No. = SC-1M1 Style 15 Insertion Depth = .080" to .110" Style 15 Component Part No. = SC-1M2	STYLE	Z	-14	(5,08) .200	-15	(4,24) .167
STYLE	Y	Z																		
-2 or -22	(3,18) .125	(7,62) .300																		
-18 or -38	(4,57) .180	(8,89) .350																		
STYLE	Z																			
-14	(5,08) .200																			
-15	(4,24) .167																			

Mates with:

SS-1, SD-1, HSS, SL,
SDL, ESS, ESD, HLS

SPECIFICATIONS

For complete specifications
see www.samtec.com?HLT

Same as HLS except:
Terminal Material:
Brass
Plating:
Au or Sn over
50μ" (1,27μm) Ni
Current Rating:
1A

Note:

This Series is non-standard,
non-returnable.

HLT	NO. ROWS	NO. PINS PER ROW	PLATING OPTION	LEAD STYLE
Total Pins = No. Rows x No. Pins Per Row		-01 thru -20 (requires both digits)	-G = 20 μ" (0,51 μm) Gold	-R
		01 thru 20 (requires both digits)	-T = Tin	-H
				-T = Short Tail

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 • Fax: 812-948-5047
SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0 • Fax: +49 (0) 89 / 89460-299
SAMTEC SCANDINAVIA • Tel: +46-84477280 • Fax: +46-847420413
SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 • Fax: 65 6841-1502
SAMTEC HONG KONG • Tel: 852-26904858 • Fax: 852-26904842
SAMTEC JAPAN • Tel: 045-475-1385 • Fax: 045-475-1340
SAMTEC KOREA • Tel: 82-31-717-5685 • Fax: 82-31-717-5681
SAMTEC SILICON VALLEY • Tel: 408-395-5900 • Fax: 408-395-1520
SAMTEC FRANCE • Tel: 01 60 95 06 60 • Fax: 01 60 95 06 61
SAMTEC CHINA • Tel: 86-21-61103766 • Fax: 86-21-61103766
SAMTEC SOUTH AFRICA • Tel: 27 11 4528112 • Fax: 27 86 6714432
SAMTEC UK • Tel: 01236 739292 • Fax: 01236 727113
SAMTEC ITALY • Tel: 39 039 6890337 • Fax: 39 039 6890315
SAMTEC INDIA • Tel: 91 80 306 21 612 • Fax: 91 80 4152 8187
SAMTEC TAIWAN • Tel: 886 02 2698-3367 • Fax: 886 02 8698-2159
SAMTEC ANZ • Tel: 613 9512 7747 • Fax: 613 9512 7745