

Spacing: 7.62 mm				unmarked		unmarked		
	100	14.32	7.62	2	25.390.3253.0	25.66	7.62	25.398.6253.0
	100	21.94	15.24	3	25.390.3353.0	33.25	15.24	25.398.6353.0
	50	29.56	22.86	4	25.390.3453.0	40.90	22.86	25.398.6453.0
	50	37.18	30.48	5	25.390.3553.0	48.52	30.48	25.398.6553.0
	50	44.80	38.10	6	25.390.3653.0	56.14	38.10	25.398.6653.0
	50	52.42	45.72	7	25.390.3753.0	63.76	45.72	25.398.6753.0
	50	60.04	53.34	8	25.390.3853.0	71.38	53.34	25.398.6853.0
	50	67.66	60.64	9	25.390.3953.0	79.00	60.64	25.398.6953.0
	50	75.28	68.58	10	25.390.4053.0	86.62	68.58	25.398.7053.0
	50	82.90	76.20	11	25.390.4153.0	94.24	76.20	25.398.7153.0
	50	90.52	83.82	12	25.390.4253.0	101.86	83.82	25.398.7253.0
Accessories:								
Coding piece (strip)	100			05.561.0053.0		05.561.0053.0		
Fixing device assembly - for screw flanges on both sides of the header	100			25.523.2453.0				

300