




Aluminum Enclosures with Coax Connectors

Die Cast Aluminum Boxes

- Coax Connectors Are 50 Ohm Nominal Impedance
- Boxes with Connectors Are Rated at 500 VRMS Max., +150°C (+302°F) Max. Except for Model 2399 Which Is Rated at 335 VRMS Max. and Model 2411 Which Is Rated at 1000 VRMS

Die Cast Aluminum Boxes
Provide excellent RF/EMI protection when used with the included cover and screws. Available with no finish or blue baked enamel per Federal Standard 595 #295109 over primer wash per DOD-P-15328. Covers are aluminum 1100-H14 with clear anodize finish per MIL-A-8625. All boxes are supplied with covers and cover screws.

Materials: Miniature, Size A, B, C, D, E, J and L — Die cast alloy A380 or A384; Size F, G, H and I — Extruded aluminum, alloy 6063-T5 or equivalent.

Stock No.	Mfr.'s Type	Box Size	Finish	EACH
885-3753	3753	Miniature	Blue Baked Enamel	6.40
885-3754	3754	Miniature	None	6.15
885-2397	2397	A	Blue Baked Enamel	6.40
885-2400	2400	A	None	5.90
885-0550	2417	B	Blue Baked Enamel	6.60
885-2428	2428	B	None	6.25
885-3601	3601	D	Blue Baked Enamel	11.70
885-3606	3606	D	None	11.40
885-0665	2901	C	Blue Baked Enamel	16.25
885-2906	2906	C	None	13.75
885-4227	4226	E	Blue Baked Enamel	42.00
885-5186	5186	E	None	39.20
885-6016	4655	J	Blue Baked Enamel	20.10
885-6015	5255	J	None	18.10
885-4903	4903	L	Blue Baked enamel	24.10
885-5203	5203	L	None	23.60
885-3301	3301	F	Blue Baked Enamel	25.30
885-3306	3306	F	None	23.20
885-0001	3311	G	Blue Baked Enamel	30.20
885-3316	3316	G	None	28.60
885-3742	3742	H	Blue Baked Enamel	37.25
885-4641	4641	I	Blue Baked Enamel	70.00

Miniature Size Box, BNC Female Each End
1st End: BNC female with solder turret terminal screws. 2nd End: Same as first end.
885-3751. Model 3751EACH 24.70

Miniature Size Aluminum Box
Blue baked enamel. **Connectors:** BNC male/female.
885-3752. Model 3752EACH 23.40

Size A Aluminum Boxes
Blue baked enamel. **Connectors:** Model 2390 — BNC female/female; Model 2391 — BNC male/female.
885-2390. Model 2390EACH 20.35
885-0525. Model 2391EACH 22.95

Size A Box, BNC Female "T"
1st End: BNC female with solder turret terminal screws. **Center:** Same as first end. 2nd End: Same as first end.
885-2392. Model 2392EACH 31.20

Size A Box, "T" Two BNC Females to BNC Male
1st End: BNC male with solder turret terminal screws. **Center:** BNC female with solder turret terminal screws. 2nd End: Same as center.
885-2401. Model 2401EACH 33.45

Size A Box, SMA Female Each End
1st End: SMA female with solder turret terminal screws. Gold plated per requirements of MIL-C-39012. 2nd End: Same as first end.
885-2399. Model 2399EACH 50.00

Size B Box, BNC Female Each End
1st End: BNC female with solder turret terminal screws. 2nd End: Same as first end.
885-3230. Model 3230EACH 20.15

Size B Box, BNC Male to BNC Female
1st End: BNC male with solder turret terminal screws. 2nd End: BNC female with solder turret terminal screws.
885-3231. Model 3231EACH 24.35

Size B Box, BNC Female "T"
1st End: BNC female with solder turret terminal screws. **Center:** Same as first end. 2nd End: Same as first end.
885-3232. Model 3232EACH 32.25

Size B Box, Isolated BNC Female Each End
1st End: Isolated BNC female with solder turret terminal screws. 2nd End: Same as first end.
885-3239. Model 3239EACH 33.60

Size B Box, Type "N" Male to Type "N" Female
1st End: Type "N" male with solder turret terminal screws. 2nd End: Type "N" female with solder turret terminal screws.
885-2411. Model 2411EACH 40.00

Size B Box, BNC Female to Type "N" Male
1st End: BNC female with solder turret terminal screws. 2nd End: Type "N" male with solder turret terminal screws.
885-2420. Model 2420EACH 40.00

Size D Box, BNC Female Each End
1st End: BNC female with solder turret terminal screws. 2nd End: Same as first end.
885-3602. Model 3602EACH 26.85

Size D Box, BNC Female to BNC Male
1st End: BNC female with solder turret terminal screws. 2nd End: BNC male with solder turret terminal screws.
885-3603. Model 3603EACH 31.10

Size C Box, BNC Female Each End
1st End: BNC female with solder turret terminal screws. 2nd End: Same as first end.
885-2902. Model 2902EACH 32.35

Size J Box, Five BNC Females
1st End: Four BNC females. 2nd End: BNC female with solder turret terminal screws.
885-4656. Model 4656EACH 47.00

Size F Box, BNC Female Each End
1st End: BNC female with solder turret screws. 2nd End: Same as first end.
885-3302. Model 3302EACH 43.00

Phenolic Boxes

Phenolic Box, 2.25" × 1" × 1"
Housing: Phenolic, black. **Cover:** XP laminated paper base phenolic, black. Includes 2 #2-56 cover screws. **Rating:** +150°C (+302°F) max.
885-2103. Model 2103EACH 4.42

Component Mounting Box, Double Banana Jack to Double Banana Plug, 2.38" × 1.53" × 1.53"
1st End: Double banana jack. Brass, bright tin plated. 2nd End: Double banana plug. Brass body, beryllium copper spring, nickel plated. Supplied with cover and cover screws. **Rating:** 5000 VDC, 15 amps, +150°C (+302°F) max.
885-2224. Model 2224EACH 12.50

Phenolic Box, 2.38" × 1.53" × 1.53"
Housing: Phenolic, black. **Cover:** XP laminated paper base phenolic, black. Includes 2 #2-56 cover screws. **Rating:** +150°C (+302°F) max.
885-2104. Model 2104EACH 4.25

Component Mounting Box, Double Banana Jack to Double Banana Plug, 1.75" × 1.44" × 0.69"
1st End: Double banana jack. Brass, bright tin plated. 2nd End: Double banana plug. Brass body, beryllium copper spring, nickel plated. Supplied with cover and cover screws. **Rating:** 5000 VDC, 15 amps, +150°C (+302°F) max.
885-2098. Model 2098EACH 12.15

Phenolic Box, 1.75" × 1.44" × 0.69"
Housing: Phenolic, black. **Cover:** XP laminated paper base phenolic, black. Includes 2 #2-56 cover screws. **Rating:** +150°C (+302°F) max.
885-2105. Model 2105EACH 4.25

Component Mounting Box, Binding Posts to Double Banana Plug, 1.75" × 1.44" × 0.69"
1st End: Double binding post. Brass, bright tin plated. Accepts standard banana plugs. Polycarbonate insulation. One black and one red. 2nd End: Double banana plug. Brass body, beryllium copper spring, nickel plated. Supplied with cover and cover screws. **Rating:** 2500 VDC, 15 amps, +115°C (+239°F) max.
885-2259. Model 2259EACH 15.15