

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC., U.S.A. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.

DWG. NO.	ZONE	REV.	DESCRIPTION	DATE	APPROVED
XX6-50X-D		D	ECN C285	09/04/01	K.C.
		E	ADD NOTE & CHANGE P/N TO RDHS COMPLIANT PER ECN D830	04/21/05	M.G.


WIRE DIAGRAM

P1		P2
1	WHITE	1
2	BLACK	2
3	RED	3
4	GREEN	4
5	YELLOW	5
6	BLUE	6

T.B.D.	GLF-466-146-505-D	GLF-121-610-022	14.0 FT [4.3 M]	44.0 IN [1117.6 MM]	WHITE
H2662-14C-ND	GLF-466-146-504-D	GLF-121-610-012	14.0 FT [4.3 M]	44.0 IN [1117.6 MM]	BLACK
T.B.D.	GLF-466-146-503-D	GLF-121-610-002	14.0 FT [4.3 M]	44.0 IN [1117.6 MM]	SILVER SATIN
T.B.D.	GLF-466-106-502-D	GLF-121-610-021	10.0 FT [3.0 M]	32.0 IN [812.8 MM]	WHITE
H2662-10C-ND	GLF-466-106-501-D	GLF-121-610-011	10.0 FT [3.0 M]	32.0 IN [812.8 MM]	BLACK
T.B.D.	GLF-466-106-500-D	GLF-121-610-001	10.0 FT [3.0 M]	32.0 IN [812.8 MM]	SILVER SATIN
T.B.D.	GLF-466-076-505-D	GLF-121-610-020	7.0 FT [2.1 M]	24.0 IN [609.6 MM]	WHITE
H2662-07C-ND	GLF-466-076-504-D	GLF-121-610-010	7.0 FT [2.1 M]	24.0 IN [609.6 MM]	BLACK
H2663-07C-ND	GLF-466-076-503-D	GLF-121-610-000	7.0 FT [2.1 M]	24.0 IN [609.6 MM]	SILVER SATIN
T.B.D.	GLF-466-056-502-D	GLF-121-610-023	5.0 FT [1.5 M]	18.0 IN [457.2 MM]	WHITE
H2662-05C-ND	GLF-466-056-501-D	GLF-121-610-013	5.0 FT [1.5 M]	18.0 IN [457.2 MM]	BLACK
T.B.D.	GLF-466-056-500-D	GLF-121-610-003	5.0 FT [1.5 M]	18.0 IN [457.2 MM]	SILVER SATIN
DIGI-KEY PART NUMBER	ID# PART NUMBER	ID# CABLE PART NUMBER	EXTENDED LENGTH "X"	RETRACTED LENGTH "R"	COLOR

TABULATION BLOCK

THIRD ANGLE PROJECTION




UNLESS OTHERWISE NOTED:
1) DIMENSIONS ARE IN INCHES (MILLIMETER)
2) TOLERANCES:
X.XX ± 0.25 [6.35]

I/O INTERCONNECT SANTA ANA, CALIFORNIA	
DR. BY: JERRY SUN DR. CHECKED: [Signature]	TITLE: 6P6C/6P6C COIL CABLE, REVERSE STYLE, CABLE ASSEMBLY P/N: H266X-XXC-ND
REV: [Signature]	PART NO: GLF-466-XX6-50X-D
ENGINEER: [Signature]	DWG NO: GLF-466-XX6-50X-D
DATE/ISSUED: [Signature]	CUSTOMER: DIGI-KEY
SA: [Signature]	REV. E
SCALE: NONE	SHEET 1 OF 1

CABLE ASSEMBLY PARTS LIST

ITEM	QTY	MFG.	ID# PART NO.	DESCRIPTION
2	*X* FT	ID#	SEE "TABULATION BLOCK"	MODULAR COIL CABLE, 26 AWG (7/34) BARE COPPER, 6CONDUCTOR, UNSHIELDED, PVC JACKET, (SEE TABULATION BLOCK FOR COLOR), RDHS COMPLIANT.
1	2 PCS	ID#	GLF-325-661-50X	CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50u" Au, FLAT TYPE EXIT, RDHS COMPLIANT.



NOTES: UNLESS OTHERWISE SPECIFIED.

1. TEST CABLE FOR ALL OPENS & SHORTS.
2. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.
3. MARK OUTSIDE OF SHIPPING BOX WITH CUSTOMER PART NUMBER.
4. PLACE BAR CODE LABEL ON THE OUTSIDE OF EACH SHIPPING BOX LABEL DETAIL SEE DWG 090-990-001.
5. ALL METRICAL SHOULD BE RDHS COMPLIANT.