



Dead Blow and Sledge Hammers



802 Dead Blow, Medium Hard Face Hammer, Recoilless, Polyurethane, Steel Tube Shaft. "GS" Sign, Cushion Grip.

- Preserves sensitive surfaces and edges
- Increases striking power
- Avoids hand fatigue

Application:

- Machine tools and gear box construction
- Sheet metal shops and repair shops

Faces polyurethane, shatterproof, wear resistant, extremely durable
Faces replaceable. Tubular handle, lacquered in blue, cushion grip.

Item No.	mm	Inch	mm	Inch	mm	Inch	oz.	pkg.
802 25	25	1.0	106	4.2	288	11.3	18	1
802 30	30	1.2	115	4.5	290	11.4	21	1
802 35	35	1.4	118	4.6	300	11.8	24	1
802 40	40	1.6	125	4.9	305	12.0	30	1
802 45	45	1.8	130	5.1	310	12.2	37	1
802 50	50	2.0	130	5.1	365	14.4	49	1
802 60	60	2.3	156	6.1	375	14.7	72	1
802 70	70	2.8	161	6.3	385	15.1	97	1



For 800 & 802 Hammers



802 Replacement Hammer Faces - Medium hard.

Item No.	mm	Inch	lbs.	pkg.
802 00	25	1.0	.04	1
802 02	30	1.2	.04	1
802 04	35	1.4	.05	1
802 06	40	1.6	.08	1
802 08	45	1.8	.12	1
802 10	50	2.0	.16	1
802 13	60	2.3	.29	1
802 16	70	2.8	.39	1



802 90 3 Piece Dead Blow Hammer Set - Medium hard.

Item No.	mm	Inch	lbs.
802 90	802 30	30	6.35
	802 40	40	
	802 50	50	




800 Dead Blow, Medium Hard Face, Recoilless, Polyurethane Face, Hickory Handle. Application:

- Tools, engineering gear box construction
- Sheet metal and repair shops, heavy industry

Steel head for incredible strength. Faces polyurethane, shatterproof, wear resistant, extremely durable. Faces replaceable. Hickory handle.

Item No.	mm	Inch	mm	Inch	mm	Inch	oz.	pkg.
800 25	25	1.0	106	4.2	320	12.5	11	1
800 30	30	1.2	113	4.4	350	13.7	16	1
800 35	35	1.4	115	4.5	355	13.9	20	1
800 40	40	1.6	123	4.8	375	14.7	26	1
800 45	45	1.8	130	5.1	380	14.9	35	1
800 50	50	2.0	134	5.3	385	15.1	44	1
800 60	60	2.3	158	6.2	420	16.5	70	1
800 70	70	2.8	158	6.2	430	16.9	91	1



800 Hickory Replacement Handles - For Dead Blow Hammers

Item No.	Fits Hammer	lbs.	pkg.
800 71	80025 25mm	.11	1
800 72	80030 & 80035 30/35mm	.19	1
800 74	80040 & 80045 40/45mm	.29	1
800 76	80050 50mm	.38	1
800 78	80060 & 80070 60/70mm	.44	1
800 79	80280 80mm	1.76	1
800 81	80299 100mm	2.31	1



802 Dead Blow Sledge, Medium Hard Face, Recoilless, Polyurethane Face, Hickory Handle. Application:

- Tools, engineering gear box construction
- Sheet metal and repair shops, heavy industry.

Faces polyurethane, shatterproof, wear resistant, extremely durable. Faces replaceable. Hickory handle.

Item No.	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
802 80	80	3.1	205	8.0	882	34.6	10.0	1
802 99	100	3.9	210	8.2	1002	39.3	15.1	1

802 Replacement Hammer Tips - Medium hard.

Item No.	mm	Inch	lbs.	pkg.
802 19	80	3.1	.06	1
802 22	100	3.9	.10	1

