




SPECIFICATION

ITEM	HP-1500	
OUTPUT POWER	CONTINUOUS POWER 1500W	SURGE POWER 3000W
STANDBY CURRENT	DC 12V < 0.7A	DC 24V < 0.6A
INPUT VOLTAGE	DC12V : 10V~15V	DC24V : 20V~30V
OUTPUT VOLTAGE	AC 100V, 110V, 120V, 220V, 230V, 240V	
OUTPUT WAVEFORM	Modified Sine Wave	
EFFICIENCY	> 85%	
※ INITIAL CHECKING	AUTO-DETECTING WRONG BATTERY CONT. ex. 12V / 24V	
※ OUTPUT REGULATION	± 5% INTELLIGENT PWM	
※ OUTPUT FREQUENCY	50Hz , 55Hz , 60Hz CRYSTAL CONTROLLED.	
※ COOLING	AUTO-OPERATION FAN	
※ OUTPUT SHORT	OUTPUT SHORT CIRCUIT PROTECTION	
※ LOW BATTERY	< 10.5V ± 0.5V or 21.5V ± 1V PRE-ALARM	< 9.5V± 0.5V or 20V ± 1V SHUT DOWN & ALARM
※ OVER HEATING	> 60℃ PRE-ALARM	> 65℃ SHUT DOWN & ALARM
※ OVER LOAD	> 1500W PRE-ALARM	> 1600W SHUT DOWN & ALARM
BATTERY POLARITY REVERSE	BY FUSE	
FUSE	DC 12V : 25A * 8PCS	DC 24V : 15A * 8PCS
AC OUTLET	2 AC OUTLETS	EUROPEAN TYPE : 1 AC OUTLET
DIMENSION (L*W*H)	400*135*79mm	
NET WEIGHT	3.3Kg	

※ MARK ARE OUR UNIQUE FUNCTIONS