


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS in.				
		A $\pm .03$	W $\pm .01$	C $\pm .015$	M $\pm .03$	H $\pm .01$
P22-2F	#2	.49 (12.45)	.20 (5.08)	.19 (4.83)	.39 (9.91)	.10 (2.54)

NOTES:

1. RECOMMENDED FOR #26-22 SOLID OR STRANDED COPPER WIRE
2. MATERIAL:
A. STAMPING - .020 (0.51) THK COPPER, TIN PLATED
3. PACKAGE QTY: STD. PKG. -C=100
BULK PKG. -M=1000
4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
5. INSTALLATION TOOLS: CT-100, CT-200
6. WIRE STRIP LENGTH: $3/16^{+1/32}_{-.0}$ (4.8 $^{+.8}_{-.0}$)



A41228_04

								 PANDUIT CORP. TINLEY PARK, ILLINOIS			
04	1/01	KMD		CAD FILE SPEC. WAS N41228AA_PCD_03				#26-22 BARREL NON-INSULATED FORK TONGUE			
03	7/95	MC		UPDATED NOTES AND DIMENSIONS	03454						
REV	DATE	BY	CHK	DESCRIPTION	ECN #	APP	PM	DRAWN BY	CHK'D	SCALE	DRAWING NO.
								DAW		NONE	A41228

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[P22-2F-M](#)