


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs/100pcs. (g)
	MIN. in (mm)	MAX. in (mm)									
PLT2EH	.50 (12.7)	2.0 (51)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	9.0 (229)	250 (1112)	EXTRA HEAVY	1.6 (722)
PLT5EH	.50 (12.7)	5.0 (127.0)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	20.1 (511)	250 (1112)	EXTRA HEAVY	3.1 (1406)
PLT6EH	.50 (12.7)	6.0 (152.4)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	22.2 (564)	250 (1112)	EXTRA HEAVY	3.6 (1633)
PLT8EH	2.5 (63.5)	8.0 (203.2)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	28.3 (719)	250 (1112)	EXTRA HEAVY	4.9 (2223)
PLT10EH	2.5 (63.5)	10.0 (254.0)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	34.2 (869)	250 (1112)	EXTRA HEAVY	5.8 (2631)
PLT12EH	2.5 (63.5)	12.0 (304.8)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	40.1 (1019)	250 (1112)	EXTRA HEAVY	6.5 (2931)

NOTES:

*1) SEE www.panduit.com FOR CURRENT PART NUMBER SUFFIX DESIGNATION AND FOR PACKAGE SIZE AND PART COLOR.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS.

PAN-TY® NON-RELEASABLE - LASHING TIES

CUSTOMER DRAWING

ITEM REVISION NAME

W10001EG/00

DATASET FILE NAME

W10001EG/00-SS-6512_REV09


UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE: IN (mm)

.x ± .1 (2.5)

.xxx ± .010 (.25)

.xx ± .02 (1.5)

ANGLES: ---



THIRD ANGLE
PROJECTION

MATERIAL:

NYLON 6/6

DRAWING NUMBER:

SS-6512

DRAWN BY

L.VALDES

DATE

7-15-77

CHK

HVP

SCALE

NONE

SHT 1 OF 1

SIZE

A

DI01000A/16