


Female Header 2,00 mm

Series

156



Rated current	1,5 A
Rated voltage	150 V _{RMS} / V _{DC}
Withstand voltage	500 V _{RMS} for one minute
Material contact	Phosphor bronze
Material insulator	High temp. thermoplast UL94V-0
Operating temperature	-40°C to +105°C
Max. processing temper.	260°C for 10 seconds

pitch
2,00

termination



mating pin
size


□ 0,50

max.
pincount
030/040/080



All dimensions in mm.

Variation



PCB Layout





1





2





3




4



5



6



* No. of contacts:
Variation 1 = 002 - 040
Variation 2 = 002 - 030
Variation 3 = 004 - 080
Variation 4 = 004 - 060
Variation 5 = 004 - 080
Variation 6 = 004 - 080

Plating:
T = Sn
F = Au

Variation (1,2,3,...)

No. of contacts *
(002,... - 080)

Plating contact (T,F)



www.mpe-connector.de

Order code:

156-2-??-0-N?X-YS0

Mating series	150	152	151	337	332	333	155
see page	3-25	3-26	3-27	3-28	3-29	3-30	3-33