




- ① HOUSING: GLASS FILLED POLYESTER; COLOR: BLACK.
- ② CONTACT: PHOSPHOR BRONZE.
- ③ NICKEL PLATE: 0.00127 [0.00050] MIN – ALL OVER.
- ④ MATTE TIN PLATE: 0.00254 [0.00100] MIN – SOLDER POSTS.
- ⑤ GOLD PLATE: 0.00076 [0.00030] MIN – CONTACT AREA.
- ⑥ NICKEL PLATE PER MIL-G-45204.
GOLD PLATE PER QQ-N-290.
- ⑦ TE PART NUMBER, DATE CODE AND CSA LOGO MAY BE MARKED
IN APPROXIMATE AREA SHOWN, EITHER SIDE.



10,11,12,14,16,18,20,22, 23,24,26,28,30,33,35,37, 39,40,41,43,45,47,49,51, 52,53	11,12	2,3,29,31,32,34,60,61	6364999-2
6	11,12	2,3,29,30,33,34,60,61	6364999-1
OMITTED PIN	KEY LOCATION	RETENTION LOCATION	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 17 AUG 05 CHK 17 AUG 05 AL FRANTUM AL FRANTUM APVD -	
DIMENSIONS: mm		NAME	
		CONNECTOR ASSEMBLY STANDARD EDGE II, 2.54 [.100] CL	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± 2°		PRODUCT SPEC 108-9039 APPLICATION SPEC 114-13018	
MATERIAL		SIZE	CAGE CODE
		A1	00779
FINISH		DRAWING NO	
		C-6364999	
CUSTOMER DRAWING		RESTRICTED TO	
		SCALE 5:1 SHEET 1 OF 1 REV B3	