

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300700024](#)
Status: **Active**
Overview: [BradPower Cordsets and Receptacles](#)
Description: BradPower D-Size (1 3/8"–M35) Male Field Attachable, 4-Pole, Straight

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
UL E258922


General
Product Family Field Attachable / Accessories
Series [130070](#)
IP Rating IP67
Material - Contact Copper Alloy
Overview [BradPower Cordsets and Receptacles](#)
Product Name BradPower D-Size
Type Field Attachable Connector
UPC 78678804606

Physical
Cable Diameter N/A
Coupling Type Internal Thread
Diagnostics / LEDs No
Diagnostics Port No
Gender Male
Keyway Single
Material - Connector Body PVC
Material - Coupling Nut Anodized Aluminum
Material - Plating Mating Gold
Net Weight 141.520/g
Orientation Straight
Poles 4
Temperature Range - Operating -20°C to +90°C
Wire Size AWG N/A

Electrical
Current - Maximum per Contact 30.0A
Voltage - Maximum 600V DC

Material Info
Engineering Number CA4006-39

Reference - Drawing Numbers
Sales Drawing SD-120336-002



EU ELV
Not Relevant

EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Low-Halogen	

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130070](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION