




VO5/24

radome Omnidirectional Antenna

Specifications

Type	omnidirectional antenna with radome
Polarization	vertical
Frequency	2400-2485 MHz
Impedance	50 ohm
VSWR	≤1.5:1
Gain	5 dBi
Connector	SMA female
Power handling	20 W
Mount	mounting bracket fits 35-50 mm mast tubes holes for wall mount
Diameter	122 mm
Length	130 mm excl mounting bracket 215 mm incl mounting bracket
Weight	190 g net, 300 g shipping
Material	mounting bracket - stainless steel radome - pvc
Color	white radome
Other	designed for indoor use

Smarteq reserves the right to change specifications without prior notice.



Elevation (E-field) radiation pattern

SMARTEQ™
■■■■■ antennas

Smarteq Wireless AB

P.O. Box 4064 | SE-182 04 Enebyberg | Sweden

www.smarteq.com

550045B

Smarteq develops and supplies high-quality antennas and antenna systems for the wireless transfer of speech and data, communication to and from vehicles and machine to machine. Our staff is fully focused on developing high-performance antennas that will continue to set new standards of excellence that will exceed our customers' expectations