




FEMALE END VIEW



SPECIFICATIONS


HOUSING MATERIAL/COLOR	GLASS FILLED NYLON/BLACK
CONTACT MATERIAL/PLATING	GOLD PLATED BRASS
COUPLING NUT MATERIAL/PLATING	ANODIZED ALUMINUM
CAP MATERIAL/FINISH	NICKEL-PLATED BRASS
GASKET MATERIAL	NITRILE (BUNA-N)
O-RING MATERIAL	NITRILE (BUNA-N)
CABLE MATERIAL	STAINLESS STEEL/NYLON COATED
RATED CURRENT [A]	9.0 A
RATED VOLTAGE [V]	600 V
MAXIMUM WIRE SIZE	16 AWG
TERMINATION METHOD	SCREW TERMINAL
CABLE GRIP RANGE	PG 9 = 6-8mm, PG 13.5 = 10-12mm
TEMPERATURE RATING	-40°C to +90°C (-40°F to +194°F)
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP 67



NOTES:

1. "/CS10359" DESIGNATES FIELD WIRABLE WITH CABLE CLOSURE CAP.

SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION	<div>THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.</div> <div>TURCK inc <i>High Technology Sensors and Automation Controls</i></div> <div>3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com</div>				
						
	MATERIAL	DRFT JBJ	DATE 02/27/02	DESCRIPTION B 4151-0/16/CS10359		
	SEE SPECIFICATIONS	APVD	SCALE 1=1.0			
FINISH	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY	UNIT OF MEASUREMENT		IDENTIFICATION NO.		REV
SEE SPECIFICATIONS		MILLIMETER [INCH]		U0878-09		B
		DO NOT SCALE THIS DRAWING		FILE: U0878-09		SHEET 1 OF 1

B	UPDATE CAP FROM THREE FLATS TO TWO	RDS	10/17/11	36728
REV	DESCRIPTION	BY	DATE	ECO NO.