

DATA SHEET

KP05 TYPE 'K' NEEDLE PROBE

Needle Probes - 3.3 mm Type 'K'

Description

This probe uses the bulbous handle to enable the sensor tip to be pushed into a semi-solid product with maximum ease of use.

Construction

Needle Probe 3.3mm Diameter by 100mm Long : Stainless Steel 316 (Food Grade)
2M curly polyurethane cable with moulded connector. Complete waterproof assembly.

Sensor Features

➤ TOTAL ENCAPSULATION TECHNIQUE FOR MAXIMUM STRENGTH AND DURABILITY.

This results in a solid handle as opposed to a hollow handle. This is particularly important as there is often damage to the handles caused by excess heat. With a hollow handle it is possible to puncture the outer plastic and damage the sensor irreparably.

➤ WATERPROOF HANDLE

Due to the total encapsulation method used, all TME probe handles are completely waterproof.

➤ TOUGH POLYURETHANE CABLE

- Polyurethane cables are used in place of the standard polyurethane for the following reasons :-
- Greater retractability
- Enhanced memory of it's curl
- Non-Toxic
- Greater mechanical strength for durability
- 12 X 0.2mm wires used internally for greater strength.
- PTFE inner insulation for strength and retractability.

➤ HIGH ACCURACY THERMOCOUPLE MATERIAL THROUGHOUT

Type 'K' Thermocouple : Class I ($\pm 1.5^{\circ}\text{C} \pm 0.5\%$)

➤ POLYPROPYLENE HANDLES

Polypropylene is an extremely tough and durable material, commonly used for milk crates, it has good low temperature performance and a relatively high melt temperature. It performs exceptionally well under chemical attack.

- WIDE AMBIENT TEMPERATURE SPECIFICATION : -30 TO 50 °C
- TIME RESPONSE (96% of value in water) : 1.6 Secs
- MEASUREMENT RANGE : -100 TO 250 °C

Cross-reference for compatible instruments

Suitable instruments for use with this probe

TME PART No	DESCRIPTION	APPLICATION
MM2000	SINGLE INPUT INSTRUMENT	HIGH ACCURACY TEMPERATURE MEASUREMENT
MM2010	MAX / MIN HOLD INSTRUMENT	HIGH ACCURACY INSTRUMENT WITH MAX, MIN AND HOLD FEATURES
MM2020	DIFFERENTIAL INSTRUMENT	DUAL INPUT INSTRUMENT FOR DIFFERENTIAL MEASUREMENTS
MM2030	THERMOCOUPLE SIMULATOR	HIGH ACCURACY SIMULATOR WITH MEASUREMENT FACILITY