

TN20-2F


BURNDY® PRODUCTS

TN20-2F

TN20-2F : NY FK 26-20 SD 1-2



ACTIVE

[Assistant](#)[Add to Favorites](#)[Email Datasheet](#) [Print Datasheet](#)

FCI Brings You More

[Contact our sales/technical support](#)[Sample request](#)[Price request](#)

Specifications

[Download document](#)**Dimensional Physical Approvals / Certifications Other Features****Dimensional**

Stud Hole (Size)	#2 #1
Tongue Width (in)	0.18 in.
Wire Insulation Grip	No
Insulation Diameter (Max)	0.098 in.

Physical

Conductor Size	20 AWG 22 AWG 24 AWG 26 AWG
Element A Index	Hand Tools
Insulation Type	Nylon
Color Code	Amber
Conductor Size (Range)	26 AWG to 20 AWG

Approvals / Certifications

Military Listed	No
UL Listed	No
CSA Certified	No

Other Features

Tape Mounted Catalog Number	Call Factory
Tongue Type	Fork
Bulk Catalog Number	YAE22N65F
UPC	78181073491
Keyword	smterm