

Isoliertüllen für Steckhülsen 2,8 mm / 4,8 mm / 6,3 mm

Douilles pour languettes

Housings for taps

2,8 mm

Werkstoff:

PA = Polyamid

PE = Polyethylen

PV = PVC (Polyvinylchlorid)

Temperaturbeständigkeit:

PA -55°C bis +105°C

PE -60°C bis +80°C

PVC -10°C bis +75°C

Matière:

PA = polyamide

PE = polyéthylène

PV = PVC (chlorure polyvinyle)

Résistant à une température de:

PA -55°C à +105°C

PE -60°C à +80°C

PVC -10°C à +75°C

Material:

PA = polyamid

PE = polyethylene


PV = PVC (polyvinylchlorid)

Temperature range:

PA -55°C up to +105°C

PE -60°C up to +80°C

PVC -10°C up to +75°C




Artikelnummer
Numéro d'article
Part-No.

3930pv

mm² **0.14-0.5 mm²**


AWG 26-22



3930pe

mm² **0.5-1 mm²**


AWG 22-18



3930pa

mm² **0.5-1 mm²**

AWG 22-18




Artikelnummer
Numéro d'article
Part-No.

3931pa

mm² **0.14-1 mm²**


AWG 26-18



39314pa

mm² **0.14-1 mm²**

AWG 26-18




39311pa

mm² **0.5-1 mm²**

AWG 22-18

4,8 mm




Artikelnummer
Numéro d'article
Part-No.

3935pe

mm² **0.5-2.5 mm²**


AWG 22-14



3935wpv

mm² **0.5-2.5 mm²**


AWG 22-14



3936pa

mm² **0.5-2.5 mm²**


AWG 22-14




39361pa

mm² **0.5-2.5 mm²**

AWG 22-14



3931PA/3.5
39314PA/4.0



3936PA