

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301040033](#)  
**Status:** **Active**  
**Overview:** [Specialty Lighting](#)  
**Description:** Haztex Hazardous Location 26W Fluorescent Hand Lamp with 16/3 SOOW Cord Type, Cord Length 15.24m (50.0')

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR39801  
 UL E30252

**General**

Product Family Portable Lighting  
 Series [130104](#)  
 Comments Class I, Division 1, Groups C and D (flammable gases and vapors); Class II, Division I, Groups F and G (ignitable dust); Class I, Zone 1, Group IIB (UL)  
 NEMA Configuration NEMA 5-15  
 Outlet None  
 Overview [Specialty Lighting](#)  
 Product Name Haztex  
 Type Hand Lamps, Specialty Light  
 UPC 78678861269

**Physical**

Cord Length - Primary 15.24m (50.0')  
 Cord Length - Secondary N/A  
 Depth 100.08mm (3.940")  
 Duty Hazardous  
 Guard Included Yes  
 Guard Type Cast Aluminum  
 Height 482.60mm (19.000")  
 Length N/A  
 Material - Globe Tempered Soda-Lime Glass  
 Material - Guard Cast Aluminum  
 Mounting Style Hand Held  
 Packaging Type Carton  
 Socket Construction N/A

**Electrical**

Bulb Type Fluorescent  
 Cord Type - Primary 16/3 SOOW  
 Lamp Type PL-C 26/41/4P  
 Lamp Wattage - Maximum 26W  
 Lumens 1800  
 On/Off Switch No  
 Voltage (Fixture) - Maximum 120VAC 60 HZ

**Material Info**

Engineering Number 1090-HZB163



Series image - Reference only

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130104 Series](#)