


NAH series

NAH -10 -472 -□

① ② ③ ④



The terminal cover is retracted inside the unit

DIN rail installation type is option

- ① Model Name
② Rated Current
③ Line to ground capacitor code: See table 1.1.

table 1.1 Line to ground capacitor code

Code	Leakage Current (Input 125/250V 60Hz)	Line to ground capacitor (nominal value)
000	5 μ A/ 10 μ A max	Not Provided
101	12.5 μ A/ 25 μ A max	100pF
221	25 μ A/ 50 μ A max	220pF
331	37.5 μ A/ 75 μ A max	330pF
471	50 μ A/100 μ A max	470pF
681	75.5 μ A/150 μ A max	680pF
102	0.13mA/0.25mA max	1000pF
222	0.25mA/0.5 mA max	2200pF
332	0.38mA/0.75mA max	3300pF
472	0.5 mA/1.0 mA max	4700pF

*1 When the line to ground capacitor code is different, the attenuation characteristic is different.

- ④ Options
D: DIN rail installation type

* The dimensions change when the option is set.
Refer to External view.

Features of NAH series


Ultra high-attenuation type of common mode noise from 10kHz to 1MHz

- Single Phase 250 VAC
- Quick and easy push-down terminal
Just connect the wires, push down and tighten the screws with a screwdriver


Specifications

No.	Items	NAH-06-472	NAH-10-472	NAH-16-472	NAH-20-472	NAH-30-472
1	Rated Voltage[V]	AC 1 ϕ 250 / DC250				
2	Rated Current[A]	6	10	16	20	30
3	Test Voltage (Terminal-Mounting Plate)	2,500 VAC (Cutoff Current = 20mA), 1minute at room temperature and humidity				
4	Isolation Resistance (Terminal-Mounting Plate)	500 VDC 100M Ω minute at room temperature and humidity				
5	Leakage current 125/250V 60Hz	0.5mA/1.0mA max				
6	Voltage drop	1.0V max				
7	Safety agency approval temperatures	-25 to +85°C (Refer to Derating Curve)				
8	Operating temperature	-40 to +85°C (Refer to Derating Curve)				
9	Operating humidity	20 to 95%RH (Non condensing)				
10	Storage temperature/humidity	-40 to +85°C/20 to 95%RH (Non condensing)				
11	Vibration	10 to 55Hz, 19.6m/s ² (2G), 3min. Period, 1hour each X, Y and Z axis				
12	Impact	196.1m/s ² (20G), 11ms Once each X, Y and Z axis				
13	Safety agency approvals	UL1283, CSA C22.2 No.8 (C-UL), DIN EN133200 VDE0565 Teil3-1, ENEC (At only AC input)				
14	Case size (without projection) /Mass	53×41×92 mm (W×H×D) /300g max (Option : -D refer to external view)				

Circuit Diagram



Derating Curve




External view


This product is shipped in the following condition, because it is equipped with push-down terminals.

- ① The terminal cover is retracted inside the unit.
- ② The screws for connecting the terminals are held in the up right position.

Standard Type




DIN rail installation Type



■Note when installing the noise filter on a DIN rail.

When the noise filter is grounded through the DIN rail, the proper noise attenuation may not be achieved.

Be sure to connect the protection earth (PE) of the noise filter body to the earth.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cosel:

[NAH-30-472](#) [NAH-30-472-D](#) [NAH-30-681](#) [NAH-30-681-D](#) [NAH-30-331](#) [NAH-30-331-D](#) [NAH-30-332](#) [NAH-30-332-D](#) [NAH-30-471](#) [NAH-30-471-D](#) [NAH-30-102](#) [NAH-30-102-D](#) [NAH-30-221](#) [NAH-30-221-D](#) [NAH-30-222](#) [NAH-30-222-D](#) [NAH-20-472](#) [NAH-20-472-D](#) [NAH-20-681](#) [NAH-20-681-D](#) [NAH-30-101](#) [NAH-30-101-D](#) [NAH-20-331](#) [NAH-20-331-D](#) [NAH-20-332](#) [NAH-20-332-D](#) [NAH-20-471](#) [NAH-20-471-D](#) [NAH-20-102](#) [NAH-20-102-D](#) [NAH-20-221](#) [NAH-20-221-D](#) [NAH-20-222](#) [NAH-20-222-D](#) [NAH-16-472](#) [NAH-16-472-D](#) [NAH-16-681](#) [NAH-16-681-D](#) [NAH-20-101](#) [NAH-20-101-D](#) [NAH-16-331](#) [NAH-16-331-D](#) [NAH-16-332](#) [NAH-16-332-D](#) [NAH-16-471](#) [NAH-16-471-D](#) [NAH-16-102](#) [NAH-16-102-D](#) [NAH-16-221](#) [NAH-16-221-D](#) [NAH-16-222](#) [NAH-16-222-D](#) [NAH-10-472](#) [NAH-10-472-D](#) [NAH-10-681](#) [NAH-10-681-D](#) [NAH-16-101](#) [NAH-16-101-D](#) [NAH-10-331](#) [NAH-10-331-D](#) [NAH-10-332](#) [NAH-10-332-D](#) [NAH-10-471](#) [NAH-10-471-D](#) [NAH-10-102](#) [NAH-10-102-D](#) [NAH-10-221](#) [NAH-10-221-D](#) [NAH-10-222](#) [NAH-10-222-D](#) [NAH-06-472](#) [NAH-06-472-D](#) [NAH-06-681](#) [NAH-06-681-D](#) [NAH-10-101](#) [NAH-10-101-D](#) [NAH-06-331](#) [NAH-06-331-D](#) [NAH-06-332](#) [NAH-06-332-D](#) [NAH-06-471](#) [NAH-06-471-D](#) [NAH-06-102](#) [NAH-06-102-D](#) [NAH-06-221](#) [NAH-06-221-D](#) [NAH-06-222](#) [NAH-06-222-D](#) [NAH-20-000](#) [NAH-20-000-D](#) [NAH-30-000](#) [NAH-30-000-D](#) [NAH-06-101](#) [NAH-06-101-D](#) [NAH-06-000](#) [NAH-06-000-D](#) [NAH-10-000](#) [NAH-10-000-D](#) [NAH-16-000](#) [NAH-16-000-D](#)