


1		2
---	--	---



VIEW B-B

POS.	NO.	CONFIGURATION
------	-----	---------------

[illegible]

1. RECOMMENDED P.C.B THICKNESS 1.60 MM
2. HOUSING MAT'L: NYLON 66, 25% GLASS REINFORCED.
3. CONTACTS: PHOS BRONZE ALLOY UNS-C51000,
Ø 0.460 ROUND WIRE, SEE TABLE FOR PLATING.
- ④ 4. METAL SHELL MATERIAL:
JIS C7521R-H OR THE EQUIVALENT, 0.2MM THICK.
5. PACKAGING PER GES-14-361, USING TUBE.
6. COMPANY LOGO LOCATED IN THIS AREA.
7. LEAD FREE PRODUCTS MEET EUROPEAN UNION
DIRECTIVES AND OTHER COUNTRY REGULATIONS AS
DESCRIBED IN GS-22-008.
8. FOR P/N -X88NLF: 30"u NI MIN, WITH SELECTICE TIN
ON SOLDER TAILS.
- ⑨ 9. EQUIVALENT THICKNESS Au AND GXT PLATING HAVE SAME
FUNCTION AND THEY ARE ALTERNATIVE BY THE CUSTOEMR .

FCI