


## PRIMO RANGE HALF ROUND PLIERS

NF E 73-102 / ISO 5745 / DIN ISO 5745



L1 1 \* Ø W 7 g

193	117340	7	3	-	165
193	117345	2	1	C2	185

### Long elbowed half round pliers

- Inner nose face ribbed for tighter grip.
- Double induction treatment of cutting edges for semi-hard wires Ø 1.6 to 160 kg/mm<sup>2</sup>.
- Orange PVC sleeve with guards.
- Nose angled at 45°.



L1 1 \* Ø W 7 g

160	117350	6	3	-	150
160	117355	1	1	C2	170

### Short nose half round straight pliers

- Double induction treatment of cutting edges for semi-hard wires Ø 1.6 to 160 kg/mm<sup>2</sup>.
- Ribbed nose for tight part gripping.
- Nose length: 50 mm.
- Shot-blasted finish, anticorrosion varnish.
- Orange PVC sleeve with guards.



L1 1 \* Ø W 7 g

160	117360	5	3	-	150
160	117365	0	1	C1	170

### Angled short half round nose pliers

- Nose angled at 45°.
- Orange PVC sleeve with guards.

## PRIMO RANGE WIRE STRIPPERS

- Fitted with an opening return spring and a setting screw.
- Stripping capacity: wires from 0.5 to 6 mm<sup>2</sup>.
- Orange PVC sleeve with guards.

L1 1 \* Ø W 7 g

150	117370	4	6	-	180
150	117375	9	3	C1	200



\* For a full EAN, add the following  
before the code: 303254

**Bost**

Catalogue 2005