

PART NAME	CLASSIC II RACK	PART No.	AGR-9572 TO AGR-9596
-----------	-----------------	----------	----------------------



MATERIAL

PANEL MOUNTING RAILS	12 GA. C.R.S.
VERTICAL RAILS & FILLERS	14 GA. STEEL
TOP, BOTTOM, & RAIL SUPPORTS	16 GA. STEEL
DOOR STIFFENER	18 GA. STEEL
SIDES & DOOR	20 GA. STEEL
TRIM EXTRUSIONS	ALUMINUM

FINISH

FRAME ASSEMBLY, SIDES & DOOR ASSEMBLY	GRAY TEXTURE
	ROYAL BLUE TEXTURE
TRIM EXTRUSIONS	CAUSTIC ETCHED & CLEAR ANODIZED WITH BLACK INSERT
PANEL MOUNTING RAILS	BLACK

MOUNTING PROVISIONS FOR OPTIONAL FAN.



PANEL MOUNTING RAILS ARE TAPPED #10-32 ON E.I.A. UNIVERSAL SPACING AND ARE FULLY ADJUSTABLE.

BOTTOM PIERCED FOR RC-7758 CASTERS.


LOAD RATING: 1200 LBS. MAX.

☒-(2) SETS OF (10) HOODED LOUVERS CENTERED ON EACH SIDE.

○-(2) SETS OF (15) HOODED LOUVERS CENTERED ON EACH SIDE.

□-(4) SETS OF (10) HOODED LOUVERS ON EACH SIDE.

△-(4) SETS OF (15) HOODED LOUVERS ON EACH SIDE.



OPTIONAL ACCESSORY

PART NO.	PANEL SPACE A	B	C	D	E	F	G	STEEL FRONT DOORS PART NO.
AGR-9572 ☒	42.000	47.312	18.500	17.000	—	38.562	46.562	AGD-932
AGR-9573 ○	52.500	57.812			—	49.062	57.062	AGD-933
AGR-9574 ○	61.250	66.562			27.531	57.812	65.812	AGD-934
AGR-9575 ○	70.000	75.312			31.906	66.562	74.562	AGD-935
AGR-9576 ○	78.750	84.062	18.500	17.000	36.281	75.312	83.312	AGD-937
AGR-9582 □	42.000	47.312	25.500	24.000	—	38.562	46.562	AGD-932
AGR-9583 △	52.500	57.812			—	49.062	57.062	AGD-933
AGR-9584 △	61.250	66.562			27.531	57.812	65.812	AGD-934
AGR-9585 △	70.000	75.312			31.906	66.562	74.562	AGD-935
AGR-9586 △	78.750	84.062	25.500	24.000	36.281	75.312	83.312	AGD-937
AGR-9592 □	42.000	47.312	30.750	29.250	—	38.562	46.562	AGD-932
AGR-9593 △	52.500	57.812			—	49.062	57.062	AGD-933
AGR-9594 △	61.250	66.562			27.531	57.812	65.812	AGD-934
AGR-9595 △	70.000	75.312			31.906	66.562	74.562	AGD-935
AGR-9596 △	78.750	84.062	30.750	29.250	36.281	75.312	83.312	AGD-937