


DIMENSIONS mm (inches)



GENERAL CHARACTERISTICS AND ROHS INFORMATION:

SEE DRAWING C-8609-0000A

TIN LEAD	LEAD FREE	
8609 396 71 13 755 000 E1	8609 396 71 13 755 E1 LF	Style C header, 96 Position, solder to board, class 2
8609 396 71 13 765 000 E1	8609 396 71 13 765 E1 LF	Style C header, 96 Position, solder to board, class 1
8609 396 71 13 H55 000 E1	8609 396 71 13 H55 E1 LF	Style C header, 96 Position, solder to board, class 2, fixing clips
8609 464 71 13 755 000 E1	8609 464 71 13 755 E1 LF	Style C header, 64 Position, solder to board, class 2
8609 464 71 13 765 000 E1	8609 464 71 13 765 E1 LF	Style C header, 64 Position, solder to board, class 1
8609 464 71 13 H55 000 E1	8609 464 71 13 H55 E1 LF	Style C header, 64 Position, solder to board, class 2, fixing clips
TIN LEAD	LEAD FREE	
8609 396 71 13 745 000 E1	8609 396 71 13 745 E1 LF	Style C header, 96 Position, solder to board, class 3
8609 396 71 13 H45 000 E1	8609 396 71 13 H45 E1 LF	Style C header, 96 Position, solder to board, class 3, fixing clips
8609 396 71 13 H65 000 E1	8609 396 71 13 H65 E1 LF	Style C header, 96 Position, solder to board, class 1, fixing clips
8609 464 71 13 745 000 E1	8609 464 71 13 745 E1 LF	Style C header, 64 Position, solder to board, class 3
8609 464 71 13 H45 000 E1	8609 464 71 13 H45 E1 LF	Style C header, 64 Position, solder to board, class 3, fixing clips
8609 464 71 13 H65 000 E1	8609 464 71 13 H65 E1 LF	Style C header, 64 Position, solder to board, class 1, fixing clips


Application specific part-numbers: See sheet 2

European Views

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 		
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	ROUILLARD	1992/05/05	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 1:1			
Eng	TARON	1992/05/05			0.XX	±0.1					
Chr	LEGARE	1992/05/05			0.XXX	±0.1					
Appr	LEGARE	1992/05/05	Product family		DIN 8609		Spec ref		-		
			title RIGHT ANGLE HEADER - STYL SOLDER TO BOARD			dwg no C-8609-0250-1		Rev. F			
			catalog no			-			CUSTOMER		sheet 1 of 1

rev	ecn no	dr	date
C	-	LEL	2002/08/28
D	L505-001	JTA	2005/03/02
E	L505-0056	LGO	2005/06/21
F	L506-0097	LGO	2006/07/11
-	-	-	-
-	-	-	-
-	-	-	-

PCB DRILLING




GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C-8609-0000A

European Views

rev	ecn no	dr	date
C	-	LEL	2002/08/28
D	LS05-001	JTA	2005/03/02
E	LS05-0056	LGO	2005/06/21
F	LS06-0097	LGO	2006/07/11
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302 ✓		tolerance std ISO 406 ISO 1101		projection 		mm 	
TOLERANCES UNLESS OTHERWISE SPECIFIED										
Dr	ROUILLARD	1992/05/05	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 1.5		
Eng	TARON	1992/05/05			0.XX	±0.1				
Chr	LEGARE	1992/05/05			0.XX' ±2'	±0.1		ECN	LS06-0097	
Appr	LEGARE	1992/05/05	Product family				DIN 8609	Spec ref -		
			RIGHT ANGLE HEADER - STYL SOLDER TO BOARD				dwg no C-8609-0250-2		Rev F	
catalog no			-				CUSTOMER		sheet 1 of 1	