


## Crocodile clips

### MICRO-SMD CLIP 1



Product	MICRO-SMD CLIP 1	
description	Spring-loaded, two-pole test clip, specially designed for SMD components. Gold-plated, hardened tip for testing circuits, flat-nosed grips for individual components, notch for gripping thin wires. Balanced spring force permits testing of large and small components. 0.64mm pin connection and electrically insulated spring.	
operating instruction	BA004	
Articlenummer	972416100	<b>Au</b>
drawing		
		
technical data		
connection	pin Ø 0.64 mm	
rated voltage <sup>(1)</sup>	30 VAC / 60 VDC	
measurement cat. acc. to IEC 61010	O <sup>(3)</sup>	
rated current <sup>(1)</sup> (consider derating curve)	1 A	
material socket	copper - beryllium, gold plated	
housing material	PBT	
temperature range acc. To IEC61010 <sup>(2)</sup>	-30 °C to +70 °C	
flammability class acc. to UL 94 (only valid for basic material of housing)	HB	
clamping range	8 mm	
standard	IEC 61010	

<sup>(1)</sup> for normal environmental conditions -5°C to +40°C

<sup>(2)</sup> contact the manufacturer for applications at deviating temperature ranges

<sup>(3)</sup> without rated measurement category, for other circuits that are not directly connected to mains  
stand: 19.06.2019