

Test Companion™ Test Kits Guide

► Each Test Companion™ Kit Is Tailored to Your Instrument

Simply find the model number of your Fluke, Hewlett-Packard, Tektronix or Wavetek meter to locate the Test Companion™ test kit that's been specifically configured to suit your instrument. Most test leads, probes, grabbers and clips are designed to


► Contact Your Local Allied Sales Representative for Pomona Electronics' New 1999 Catalog

conform to IEC1010 specifications. Each kit is expressly tailored to assure reliable testing and added functionality for your meter.

Model	Kit
Fluke Series I and II ScopeMeter®	6120
Fluke 20 and 70 Series II DMM	6166, 6162
Fluke 80 Series DMM	6112A, 6174

Model	Kit
Hewlett-Packard HP 34401A Bench Meters	6200
Hewlett-Packard HP 54600B and 54603B Series Oscilloscopes	6236
Tektronix TAS 220/250 and TDS 310/320 Oscilloscopes	6237

Test Companion™ Test Kits



Pomona's original Test Companion™ kits are supplied in durable Cordura carrying cases and tri-fold pouches, ready for finger-tip access whether carried on your shoulder or carried in your tool box. Extra compartments carry other tools, schematics, handbooks and anything else you may need in the lab, the field or the plant.

Select from Pomona's newest bench DMM and oscilloscope Test Companion® kits. Each kit contains an assortment of accessories specifically selected to work with your instrument. They are provided in durable Cordura carrying cases featuring handy zippered compartments for kit contents and more. Compact yet spacious, they strap-on quickly providing a total storage compartment for bench meter or scope test accessories and handbooks.

Test Companion™ Test Kits for Fluke® Test Tools

6112A Deluxe Test Companion™ Kit for Fluke 80 Series DMM

- Medium Alligator Clip Set
- Giant Heavy Duty Alligator Clip Set
- Test Probe Set with Banana Plug Tip
- Flexible Test Lead Set, Right Angle to Straight Banana Plug
- Maxigrabber® Set with Pincer Tip
- Modular Electronic Test Probe Kit

Includes large briefcase style Cordura carrying case plus the IEC1010-compliant test accessories listed.
885-6392, 6112AEACH 185.00

6120 Deluxe Test Companion™ Kit for Fluke Scopemeter®

- Medium Alligator Clip Set
- Giant Heavy Duty Alligator Clip Set
- Test Probe Handle Set with Banana Plug Tip
- Flexible Test Lead Set, Right Angle to Straight Banana Plug
- Maxigrabber® Set with Pincer Tip
- Maxigrabber® Set with Jaws
- Fully Insulated Oscilloscope Probes

Includes large briefcase style Cordura carrying case plus the IEC1010-compliant test accessories listed.
885-6252, 6120EACH 375.00

6166 Test Companion™ Kit for Fluke 20 and 70 Series II DMM

- Medium Alligator Clip Set
- Flexible Test Lead Set, Right Angle to Straight Plug
- Modular Electronic Test Probe Set
- Minigrabber® Test Clip Leads
- Extended Tip Adapter
- IC Test Tip Adapter
- Spade Lug with Jack

Includes shoulder pack style Cordura carrying case and the test accessories listed.
885-6166, 6166EACH 91.00

6174 Test Companion™ Kit for Fluke 80 DMM

- Medium Alligator Clip Set
- Flexible Test Lead Set, Right Angle to Straight Banana Plug
- Modular Electronic Test Probe Set
- Minigrabber® Test Clip Leads
- Extended Tip Adapter
- IC Test Tip Adapter
- Spade Lug with Jack
- Micrograbber® Test Clip to Pop Jack
- SMD Grabber Test Clip to Pop Jack
- SMD Test Tweezer to Sheathed Banana Plugs

Includes shoulder pack style Cordura carrying case and the test accessories listed.
885-6174, 6174EACH 119.00

6162 Basic Test Companion™ Kit for Fluke 20 and 70 Series II DMM

- Medium Alligator Clip Set
- Test Probe Handle Set with Banana Plug Tip
- Flexible Test Lead Set, Right Angle to Straight Banana Plug
- Insulated Spade Lug Set

Includes tri-fold style Cordura pouch and the IEC1010-compliant test accessories listed.
885-6162, 6162EACH 40.00

Test Companion™ Test Kits for Hewlett-Packard® Instruments

6200 Deluxe Test Companion™ Kit for Hewlett-Packard HP 34401A Bench Meters

- Medium Alligator Clip Set
- Flexible Test Lead Set, Straight to Straight Banana Plug
- Modular Electronic Test Probe
- Minigrabber® Test Clip Leads
- Minipincer® Test Clip Leads
- Extended Tip Adapter
- IC Test Tip Adapter
- Spade Lug with Jack

Includes probe, test clips and adapter with pop jack connector for easy, secure attachment. Miniature IC test tip adapter allows probing of DIPs without shorting adjacent legs. Low-profile Cordura strap-on carrying case holds test accessories, manuals and miscellaneous items. Includes the test accessories listed.
885-6203, 6200EACH 112.00

6236 Test Companion™ Kit for Hewlett-Packard HP 54600B and 54603B Series Oscilloscopes

- Oscilloscope Probes X1/X10, 15/100 MHz (2 Probe Sets)
- BNC Male (Cable Assembly) with Molded Strain Relief
- BNC Female to Minigrabber® Test Clips

Includes lightweight Cordura strap-on carrying case and the test accessories listed.
885-6236, 6236EACH 160.00

Test Companion™ Test Kits for Tektronix® Instruments

6237 Test Companion™ Kit for Tektronix TAS 220/250 and TDS 310/320 Oscilloscopes

- Oscilloscope Probes X1/X10, 15/100 MHz
- BNC Male with Molded Strain Relief, Each End
- BNC Female to Minigrabber® Test Clips

Includes low profile Cordura strap-on carrying case and the test accessories listed.
885-6237, 6237EACH 160.00

Cables for Telecommunications Testing


Bantam to Bantam Cable



Rating: 300 VRMS, +50°C (+122°F) max. Cable Type: 2 cond. shielded twisted pair, 0.180" O.D.

Stock No.	Mfr.'s Type	Length (In.)	Terminal Plating	EACH
885-4279	4279-36	36	Brass	24.90
885-1000	4279N-36	36	Nickel	27.40
885-4281	4279-60	60	Brass	26.55
885-1001	4279N-60	60	Nickel	29.20

Bantam Plug to Alligator Test Clips



Rating: 150 VRMS, +50°C (+122°F) max. Cable Type: 2 cond. shielded microphone, 0.180" O.D. Fits equipment with Bantam style jacks.

Stock No.	Mfr.'s Type	Length (In.)	EACH
885-5026	5026-36	36	28.45
885-5027	5026-60	60	29.95


Bantam Plug to WE310 Plug



Rating: 300 VRMS, +50°C (+122°F) max. Cable Type: 2 cond. shielded twisted pair 0.180" O.D.

Stock No.	Mfr.'s Type	Length (In.)	Terminal Plating	EACH
885-4280	4280-48	48	Brass	58.00
885-1002	4280N-48	48	Brass	63.80
885-4287	4280-60	60	Nickel	58.00
885-1003	4280N-60	60	Nickel	63.80

WE310 Phone Plug Cable



Rating: 300 VRMS, Cable Type: 2 cond. shielded twisted pair, 0.231" O.D. or 2 cond. twisted pair.

Stock No.	Mfr.'s Type	Length (In.)	EACH
885-1005	2524-A-48	48	34.40
885-1006	2524-A-60	60	34.40


WE310 Phone Plug to Minigrabbers®



Rating: 300 VRMS, +50°C (+122°F) max. Cable Type: 2 cond. shielded twisted pair cable.

885-4032	4812-J-60	60	36.00
----------	-----------	----	-------

WE310 Phone Plug to Alligator Test Clips



Rating: 150 VRMS, +50°C (+122°F) max. Cable Type: 2 cond. twisted pair, 0.250" O.D.

885-3353	3352-A-60	60	32.25
885-1007	3352-A-120	120	35.00

Same Day Shipments For Product In Stock

ALLIED ► 1003