


PAN-FLEX™ Flat Cable

- in 2.54 mm and 3.96 mm spacing with color identification circuit position 1.
- flexible PVC coated cable, tinned (7 strands) to UL style 2651.
- PVC insulation – grey RAL 7032
- Temperature Range -20° / +105° C
- U.L. Flammability VW-1


Part Number

No. of Circuits	2 – 28			2 – 24		
Flat cable	.100", (2.54 mm)			.156", (3.96 mm)		
Version	AWG 22	AWG 24	AWG 26	AWG18	AWG 20	AWG 22
Non pre-bonded**	100F22V □□CR*	100F24V □□CR*	100F26V □□CR*	156F18V □□CR*	156F20V □□CR*	156F22V □□CR*
Pre-bonded***	100PF22V □□CR*	100PF24V □□CR*	100PF26V □□CR*		156PF20V □□CR*	156PF22V □□CR*
Color Code	Red	Black	Blue	orange	Brown	Red



- * Roll length = CR = 100 ft (6-24 Ckt) DR = 500 ft (2-5 Ckt)
- ** designed for connector/connector applications
- *** designed for connector/board applications (no pre-tinning necessary)
- AWG 18, No. of conductors 2 to 16
- Complete part number with number of circuits

Spacing mm
 .100 (2.54 mm) .625 (15.88)
 .156 (3.96 mm) .700 (17.78)



Increments N1 to N12

- Available in increments of 1" (25.4 mm) spacing to 12" (304.8 mm) spacing, with only one spacing interval per roll.
- Other notched spacing intervals available upon request.

Part Number Example

N1 = 1" (25.4 mm)
 N2 = 2" (50.8 mm)
 N3 = 3" (76.2 mm)
 N11 = 11" (279.4 mm)
 N12 = 12" (304.8 mm)

100PF24V □□N3-CR

□□= Number of Circuits