

MODEL TL-4955



International size reference: 2/3AA, ER14335

TECHNICAL DATA

(Typical values @+25°C for batteries stored for one year or less)



■ Nominal capacity @ 0.5 mA, to 2V	1.65 Ah
■ Rated voltage	3.6 V
■ Maximum recommended continuous current	35 mA
■ Maximum 1 sec. pulse capability	75 mA
■ Weight	12.5 g (0.441 oz)
■ Volume	5.2 cc
■ Operating temperature range	-55 °C to +85 °C
■ U.L. Component Recognition, MH 12193	

***TADIRAN
LITHIUM
BATTERIES***



AVAILABLE TERMINATIONS

SUFFIX- /S STANDARD	15-4955-21000
SUFFIX- /T SOLDER TABS	15-4955-31000
SUFFIX- /P AXIAL PINS	15-4955-41000
SUFFIX- /PT2 RADIAL PINS	15-4955-36000
SUFFIX- /TP POLARIZED TABS	15-4955-52000
SUFFIX- /PT POLARIZED TABS	15-4955-53000



XOL - Extended Operating Life

Note: Any presentations in this data sheet concerning performance are for information purpose only and are not construed as warranties either expressed or implied, of future performance.

ECN 1501174 Rev. C 01/06