




13	12	11	10	9	8	7	6	5	4	3	2	1
MATERIAL NUMBER LOOSE PCS	ENGINEERING NUMBER LOOSE PCS	MATERIAL NUMBER ON STRIP	ENGINEERING NUMBER ON STRIP	MATERIAL NUMBER ON TAPE	ENGINEERING NUMBER ON TAPE	WIRE SIZE		ACCEPTS TAB SIZE				
190020044	C-5265	190020046	C-5265Z	190020045	C-5265T	12-10 AWG /2.7-6.6 mm ²		.250 X.032 /6.35 X 0.81				

D1


D1



PARTS ON TAPE



SECTION A-A



SALES DRAWING

NOTES:

- MATERIAL: TERMINAL BRASS .018/0.46 THK REF.
TERMINAL PLATING: ELECTRO TIN
FERRULE: BRASS
FERRULE PLATING: ELECTRO TIN
INSULATION: NYLON 94V2 COLOR YELLOW.

2. MWID = MAXIMUM WIRE INSULATION DIAMETER

- PART IS RoHS COMPLIANT

ADD DIMS. RMV 19606 EC NO: WNA2011-0458 DRWNE:THRODAHL 2011/03/08 CHKD:JMACNEIL 2011/03/08 APPR:JMACNEIL 2011/07/05	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE ---	DESIGN UNITS INCH	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY BENDERLE	DATE 2005/04/15	TITLE AVIKRIMP FEMALE FIQD 12-10 AWG EXPANDED FLARE				
			4 PLACES	± ---	± ---	CHECKED BY R DEROSS	DATE 2005/04/15					
			3 PLACES	± ---	± .005	APPROVED BY DATE		MOLEX MOLEX INCORPORATED				
			2 PLACES	± 0.13	± .01	R DEROSS 2005/04/15						
			1 PLACE	± 0.25	± ---	MATERIAL NO. SEE CHART		DOCUMENT NO. SD-19002-005		SHEET NO. 1 OF 1		
			ANGULAR ±1/2°		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			