

HBL15W47 -- Elastogrip Series Connector Body



2R3W, 15A 125V, 5-15R, Yellow Elastomer, Watertight

Product Specifications

Product Type



Connectors

Body Style

Straight

Standard

NEMA

Amperage

15A

Voltage

125V

Poles and Wires

2 Pole, 3 Wire Grounding

Wiring Method

Back Wire

Hospital Grade ?

No

Plug/Connector Grade

Elastogrip

Enhancement

Water Tight


Color



Yellow

NEMA No.	5-15R
Cord Dia.	.300"-.655" (7.6-16.6)
Description	Straight Blade Connector
Type	2 Pole, 3 Wire, Grounding
Rating	15A, 125V
Certification	UL Listed to UL498 File E1706, CSA Certified to C22.2 No. 42 File 280
IP Suitability	IP20
Housing Material	PVC-Yellow
Retainer Material	Polycarbonate-Clear
Cord Clamp Material	Nylon-Yellow
Terminal Screw Material	#8-32 Brass, Multiple Drive
Ground Screw Material	#8-32 Brass, Multiple Drive (Green)
Wire Clamps Material	0.062" (1.6) Steel - Ni Plated
Body Holding Screws	Steel Multiple Drive
Contact Holder Material	Nylon-Natural
Power Contacts Material	.040" (1.0) Copper Alloy
Dielectric Voltage	Withstands 2,000V minimum.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%..
Terminal Identification	Terminals identified in accordance with UL498 (Brass, White, Green).
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only.
Product Identification	Ratings are a permanent part of the device.
Flammability	UL 94 HB or better.
Operating Temperatures	Maximum continuous 75°C, minimum -40°C (w/o impact).
M Drawings	Click here for M-Drawing
Catalog Page	Click here for catalog page A18
Brochures	Click here for product brochure
Hubbellnet	Click here for Hubbellnet
Catalog Section	Click here for Section-A

UPC Number	78358501302
Weight in LBs	0.3



Hubbell Incorporated (Delaware)
185 Plains Road
Milford, CT 06460-2420
Ph: (203) 882-4800
Fax: (800) 255-1031

