


CATALOG LISTING
BZF1-2RN2-LH
PAGE 1 OF 1
REPLACES

ISSUE
19

REVISIONS

A	CO-73287M	01APR10	CHECK
16 MAY 95			
B	CO81513B	01APR10	CHECK
6 MAR 97			
C	0063051	01APR10	CHECK
25 MAY 95			
JJA			
16 MAY 95			
GJW			

RASTER
DRAWN



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

CHARACTERISTICS	ELECTRICAL DATA
OPERATING FORCE ----- 2 LB MAX	CONTACT ARRANGEMENT S P D T
RELEASE FORCE ----- 1/4 LB MIN	
PRETRAVEL ----- .219 MAX	
DIFFERENTIAL TRAVEL ----- .008 MAX	
OVERTRAVEL ----- .219 MIN	
BASIC SWITCH REPLACEMENT BZ-2R708-P7	

THIRD ANGLE PROJECTION

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE

ONE PLACE	(.0)	± .030
TWO PLACE	(.00)	± .015
THREE PLACE	(.000)	± .005
ANGLES		±

WEIGHT .670 LB

NOTES

1 - ROLLER LEVER BRACKET ASSEMBLY MAY BE SET IN ANY POSITION AROUND AXIS OF PLUNGER

2 - 8-32 UNC X (.219) BINDER HEAD, COMBINATION, TERMINAL SCREWS AND CUP WASHERS