




REV.	DATE	DESCRIPTION
NC	10/28/99	INITIAL RELEASE
A	01/31/07	UPDATE DRAWING FORMAT



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex						
7						DRAWN	G.R.S.						01/31/07	
6						CHECKED			PART DESCRIPTION 7/16 FEMALE TO FEMALE BULKHEAD ADAPTER					
5	COVER	PE	BLUE	1		ISSUED								
4	NUT	BRASS	NEXCOTE	1		SHEET	1 OF 1		PART NO. 272174					
3	CONTACT PIN	BER. COPPER	SILVER	1										
2	INSULATOR	TEFLON	NATURAL	1					DWG. NO. 272174.DWG					
1	BODY	BRASS	NEXCOTE	1										
	DESCRIPTION	MATERIAL	FINISH	QTY		CAD FILE			REV.	A	SIZE	A	SCALE	NA
						C:/272/272174.DWG								