



Rating	16A 125VAC		Mounting Hole			Circuit Diagram	
	10A 277VAC 3/4HP						
	21A 14VDC						
Contact Resistance	50m ohm Max.						
Insulation Resistance	DC 500V 100M ohm Min.						
Dielectric Strength	AC 1500V 1 minute						
Switch Function	2P SPST ON-OFF						
Operation Temperature	-20°C~85°C						
			Thickness	X	Y		
			0.75~1.25	21.2+0.1	36.6+0.1		
			1.25~2	21.2+0.1	36.8+0.1		
			2~3	21.2+0.1	37.0+0.1		






Material:

Frame: Black, Nylon#66

Actuator: Black, Nylon#66

Printed: None

Water proof and dust proof to fit IP-56



DATE CODE

RoHS Compliant

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 1/15/10

Rev. 1

Unit: mm

Checked By: GG

Title: **ROCKER SWITCH**

CW P/N: **GRB263A0BBNN**