

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [1301080142](#)  
**Status:** **Active**  
**Overview:** [Wide-Area Lighting Products](#)  
**Description:** Super-Safeway 27W Fluorescent Machine Light, Magnet Mount with 18/3 SJTOOW Cord Type, Overall Cord Length 4.57m (15.0')

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR85374  
UL E174254

**General**

Product Family Portable Lighting  
Series [130108](#)  
NEMA Configuration NEMA 5-15  
Outlet None  
Overview [Wide-Area Lighting Products](#)  
Product Name Super-Safeway  
Type Wide Area Lamps  
UPC 78678861252

**Physical**


Cord Length - Primary 4.57m (15.0')  
Cord Length - Secondary N/A  
Depth 76.20mm (3.000")  
Duty Industrial  
Guard Included No  
Guard Type N/A  
Height 57.15mm (2.250")  
Length 552.45mm (21.750")  
Material - Globe Clear Polycarbonate  
Material - Guard Nitrile Rubber 80 Shore A  
Mounting Style Magnetic-Bracket  
Packaging Type Carton  
Socket Construction N/A

**Electrical**

Bulb Type Fluorescent  
Cord Type - Primary 18/3 SJTOOW  
Lamp Type PL-L 27/41  
Lamp Wattage - Maximum 27W  
Lumens 2000  
On/Off Switch Yes  
Voltage (Fixture) - Maximum 120VAC 60 HZ

**Material Info**

Engineering Number 1093-3MM



Series image - Reference only

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

|                 |              |
|-----------------|--------------|
| China ROHS      | Not Reviewed |
| ELV             | Not Reviewed |
| RoHS Phthalates | Not Reviewed |

**Search Parts in this Series**

[130108](#) Series