

AULT SPECIFICATIONS

12-20VA Wall Plug Series

INPUT

Voltage	230 VAC
Line Frequency	50 Hz
Configuration	Euro Wall Plug, No Ground

OUTPUT

Model Number	Rated Output Volts AC	Output Current Amps	Max VA	Agency Approvals
A48-062667-A000G	6	2.67	16.0	EN60950
A48-072286-A000G	7	2.29	16.0	EN60950
A48-082000-A000G	8	2.00	16.0	EN60950
A48-091778-A000G	9	1.78	16.0	EN60950
A48-101600-A000G	10	1.60	16.0	EN60950
A48-111455-A000G	11	1.46	16.0	EN60950
A48-141143-A000G	14	1.14	16.0	EN60950
A48-151333-A000G	15	1.33	20.0	EN60950
A48-161000-A000G	16	1.00	16.0	EN60950
A48-180889-A000G	18	0.89	16.0	EN60950
A48-200750-A000G	20	0.75	15.0	EN60742
A48-220727-A000G	22	0.73	16.0	EN60950
A48-240833-A000G	24	0.83	20.0	EN60742

*To be assigned at time of order placement.

ELECTRICAL

Topology	Step Down AC/AC Transformer
Dielectric Withstand Protection	3000 VAC primary-secondary Current, Thermal or Energy Limiting
EMI CE	Complies with EMC Directives CE Compliant

ENVIRONMENTAL

Operating Temperature	0° to 40° C with no derating
Storage Temperature	-30° to +85° C
Relative Humidity	5% to 95% non-condensing
Altitude	0 - 10,000 feet
Cooling	Convectional-non vented case

MECHANICAL

Case and Dimensions	A48 - Euro Wall Plug 81 L X 55 W X 48 H (mm) 3.2 L X 2.2 W X 1.9 H (in)
Case Material	Black 94V1 Polycarbonate
Weight	18 ounces, 520 grams, (excluding cord)
Cord and Connectors	6 ft., 2 Conductor, 22-24 AWG, Ault #3 Connector Other connectors are also available.

WARRANTY

1 Year