

[Twisted Pair & Flat
Phone Cable](#)[Fiber Optic Cable](#)[Coaxial Cable](#)[Electrical and Industrial](#)[Bench/Other Hand Tools](#)[What's New](#)[Electrical and Industrial > Crimpers > 1600 Series](#)[We also suggest](#)

1600 Series Professional Wire Ferrule Crimper

Part number: 1647 Technical

Part numbers

Tool & Die: 1647

Die only: 2681

Description

Professional-quality crimping tool for insulated and non-insulated wire ferrules with a range of 20-10 AWG (0.5-6.0 mm²).

Features

- Ferrules' crimp conforms to DIN 46228 Pt. 1 and 4
- Ferrule insertion from the side of the tool
- Single tool for entire wire range (no additional dies are required)
- Durable steel construction for long life
- Ergonomic handles for low-effort operation

Type

20-10 AWG (.5-6 mm²) stranded wire

Crimp size

20-10 Trapezoid

Connector style

DIN or US type wire ferrules

Connector type

Insulated & non-insulated wire ferrules



SealTite® Pro for
the Smart Home
A/V Kit



CST Pro Coax
Stripper 3-Level
(Green Cassette:
.279/.201)



SealTite® ProM
Coax Crimper



LAN & A/V
Cable-Check™



PowerPlay® PT-
540